

# PHILIPS

## Star Ceiling/Wall Spotlight 2x 11.5W

Ceiling/Wall Spotlights

2200-2700K



White

Dimmable; WarmGlow

Easy to install with ClickFix



56242/31/P0



## The more you dim, the warmer the light

Change your room ambience to suit whatever you're doing. With Philips WarmGlow LED spots, you can smoothly dim to the right light level – from a bright functional light to an inviting, cosy, warm glow. The more you dim, the warmer the light.

### Lighting for your convenience and peace of mind

- ClickFix easy mounting
- Get high-quality LED light, while saving energy
- Lamp lifetime for up to 30 years of use
- Instant brightness when switched on
- High light output - 1,000 lumen
- Designed for the comfort of your eyes
- Integrated LED light
- 5-year warranty for peace of mind

### Versatile lighting for every moment of your day

- Change the ambience with a twist of your dimmer

### Superior design for an optimal light effect

- Long-lasting, high-quality materials
- Adjustable spot head for maximum flexibility
- The perfect light beam for accent lighting

# Highlights

## ClickFix easy mounting



Install your spot light easily and by yourself. Thanks to ClickFix, no extra pair of hands is needed. Simply mount the bracket to the ceiling, connect the wires, then click and fix the lamp in one go.

## Energy-saving LED light

LED lights save up to 80% energy compared to traditional lighting with the same light output. When you buy a Philips LED lamp or light lamp, you start saving money straight away. For each light source you replace with a LED light, you will see immediate returns on a lower energy bill.

## Lifetime for up to 30 years

LED lights last longer, avoiding the hassle of frequent light source replacement. This significantly reduces waste, but also saves you money in the long term.

## Instant brightness

There is no need to wait with Philips LED spots. They provide their full level of brightness immediately upon switching on. Their true incandescent-like warm white light instantly creates a cosy, inviting atmosphere.

## High light output - 1,000 lumen

Brighten up your home with high-quality light

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Integrated LED light

This spot has an integrated high-quality LED light that provides optimal light output.

## 5-year warranty

All our spot lights are built to last. They come with a full 5-year warranty on the complete product, ensuring you will enjoy long-lasting quality lighting every day.

## Warm Glow dimmable light

Change your room ambience to suit whatever you're doing. With Philips Warm Glow LED spots, you can create the perfect ambience with a twist of your dimmer. Dim smoothly from 2,700 K functional bright light down to 2,200 K inviting warm light for a cosy atmosphere. The more you dim, the warmer the light.

## High quality material

This spot light is made of long-lasting, high-quality materials with superior finishing. This ensures a solid and durable product that will enhance and light up your home for many years to come.

## Easy-to-adjust spot head

The adjustable spot head is designed to direct the light where you need it most.

## Perfect for accent lighting

Modern lighting with a familiar wide-angle light output (40 degrees), this LED spot is suitable for both accent lighting and general-purpose lighting. It is ideal for use in kitchens, living rooms and dining rooms.

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Colour: White
- Material: Metal

**Durability**

- Number of switch cycles: 50,000
- Nominal lifetime: 30,000

**Environmental**

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

**Extra feature/accessory incl.**

- Adjustable spot head: Adjustable – rise and fall
- click!FIX mounting: Yes
- Defined light beams: Yes
- LED integrated: Yes

**Light characteristics**

- Colour rendering index (CRI): 80
- Colour temperature: 2200-2700 K
- Luminous efficacy (rated) (nom.): 111

**Miscellaneous**

- Especially designed for: Kitchen, Bedroom, Dining Room, Living Room, Office, Hall
- Style: Contemporary
- Type: Ceiling/Wall Spotlights
- EyeComfort: Yes
- Extra Features: Dimmable, WarmGlow

**Product dimensions and weight**

- Net weight: 0.530 kg
- Overall height: 85 mm
- Overall length: 240 mm
- Overall width: 70 mm

**Service**

- Warranty: 5 year(s)

**Technical specifications**

- Total lumen output fixture: 1000
- Bulb technology: LED
- Light colour: Soft white light
- Mains power: AC 220-240
- Fixture dimmable: Yes
- Energy class included light source: F
- Wattage bulb included: 11.5
- IP code: IP20
- Class of protection: Class I – Earthed
- Light source replaceable: No
- Number of light sources: 2

**The bulb**

- Software upgradable: No

**What's supported**

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

**Packaging dimensions and weight**

- EAN/UPC – product: 8718696154632
- Net weight: 0.53 kg
- Gross weight: 0.58 kg
- Height: 29.8 cm
- Length: 11.3 cm
- Width: 11.3 cm



Issue date: 2026-06-24  
Version: 0.717

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)