

PHILIPS

Star Ceiling/Wall Spotlight 4x 22W

Ceiling/Wall Spotlights

2700K

Aluminium

Dimmable

High quality material

56244/48/16



Smooth dimming, from bright to soft light

Sometimes you feel like a change in ambience to suit whatever you're doing. With Philips LED dimmable spots, you can smoothly dim to the right light level – from bright and functional for everyday tasks, to a soft light for relaxed time.

Lighting for your convenience and peace of mind

- Get high-quality LED light, while saving energy
- Lamp lifetime for up to 30 years of use
- Instant brightness when switched on
- Warm white light helps you create a comfortable atmosphere
- High light output – 2,000 lumen
- Designed for the comfort of your eyes
- Integrated LED light
- 5-year warranty for peace of mind

Versatile lighting for every moment of your day

- Dims smoothly from 100% bright down to 10% soft light

Superior design for an optimal light effect

- Long-lasting, high-quality materials
- Adjustable spot head for maximum flexibility
- The perfect light beam for accent lighting

Highlights

Energy-saving LED light

LED lights save up to 80% energy compared to traditional lighting with the same light output. When you buy a Philips LED lamp or light lamp, you start saving money straight away. For each light source you replace with a LED light, you will see immediate returns on a lower energy bill.

Lifetime for up to 30 years

LED lights last longer, avoiding the hassle of frequent light source replacement. This significantly reduces waste, but also saves you money in the long term.

Instant brightness

There is no need to wait with Philips LED spots. They provide their full level of brightness immediately upon switching on. Their true incandescent-like warm white light instantly creates a cosy, inviting atmosphere.

Warm white light

Light can have different colour temperatures, indicated in units called kelvins (K). Lamps with a low kelvin value produce a warm, cosy light, while those with a high kelvin value produce a cool, more energising light.

High light output – 2,000 lumen

Brighten up your home with high-quality light

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Integrated LED light

This spot has an integrated high-quality LED light that provides optimal light output.

5-year warranty

All our spot lights are built to last. They come with a full 5-year warranty on the complete product, ensuring you will enjoy long-lasting quality lighting every day.

Smooth and deep dimming

Change your room ambience to suit whatever you're doing. With the Philips Dimmable LED spots you can easily adjust the light brightness at a turn of your dimmer. Dim smoothly from 100% bright light for functional activities, down to 10% soft light for relaxed free time.

High quality material

This spot light is made of long-lasting, high-quality materials with superior finishing. This ensures a solid and durable product that will enhance and light up your home for many years to come.

Easy-to-adjust spot head

The adjustable spot head is designed to direct the light where you need it most.

Perfect for accent lighting

Modern lighting with a familiar wide-angle light output (40 degrees), this LED spot is suitable for both accent lighting and general-purpose lighting. It is ideal for use in kitchens, living rooms and dining rooms.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Colour: Aluminium
- Material: Aluminium

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 30,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- 5 year warranty on the LED module: Yes
- Adjustable spot head: Yes
- Defined light beams: Yes
- LED integrated: Yes

Light characteristics

- Colour rendering index (CRI): 80

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Hallway
- Style: Contemporary
- Type: Ceiling/Wall Spotlights
- EyeComfort: Yes
- Extra Features: Dimmable

Other characteristics

- Efficacy: 111 lm/W

Product dimensions and weight

- Net weight: 1.090 kg
- Height: 8.2 cm
- Length: 56 cm
- Width: 6.0 cm

Service

- Warranty: 5 year(s)

Technical specifications

- Total lumen output fixture: 2000
- Light colour: 2700
- Mains power: AC 220-240
- Fixture dimmable: Yes
- Energy class included light source: F
- Wattage bulb included: 22
- IP code: IP20
- Class of protection: Class I
- Light source replaceable: No
- Number of light sources: 4

Packaging dimensions and weight

- EAN/UPC – product: 8718291444916
- Net weight: 1.09 kg
- Gross weight: 1.23 kg
- Height: 57.8 cm
- Length: 7.3 cm
- Width: 9.3 cm



Issue date: 2025-06-13
Version: 0.1468

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com