

PHILIPS

Mauve Ceiling
Light 17 W Square

Ceiling Lights

4000K

White



8718696162811



Comfortable LED light that's easy on your eyes

Philips LED luminaires provide light that is designed for the comfort of your eyes

Light effect

- This ceiling light features Interlaced Optics technology, cleverly redistributing the light to enhance your overall lighting experience. This fixture's lens has a pyramid micro-structure that diffuses and evenly distributes the light, making it easier on the eyes.

Easy to experience

- Easy installation

Light effect

- Uniform light distribution

Premium quality

- Easy to clean

Highlights

Interlaced Optics

This ceiling light features Interlaced Optics technology, cleverly redistributing the light to enhance your overall lighting experience. This fixture's lens has a pyramid micro-structure that diffuses and evenly distributes the light, making it easier on the eyes.

Easy installation

No more hassle with installation. Just fix or hang securely on the wall or ceiling, and plug it in. Your new light fitting is now ready to light up your room!

Easy to clean

Smooth and easy-to-clean materials mean your home always looks attractive from floor to ceiling.

Uniform light distribution

Throw light across your rooms in an even and uniform manner.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Rectangle

Design and finishing

- Colour: White
- Material: Metal, Plastic

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 15,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Warm-up time to 60% light: 2
- Luminous efficacy (rated) (nom.): 117

Miscellaneous

- Especially designed for: Kitchen, Bedroom, Dining Room, Garage, Living Room, Office
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes

Other characteristics

- Lamp current: 150 mA

Power consumption

- Power factor: 0.5

Product dimensions and weight

- Net weight: 0.53 kg
- Overall height: 70 mm
- Overall length: 320 mm
- Overall width: 320 mm

Service

- Warranty: 5 year(s)

Technical specifications

- Total lumen output fixture: 2000
- Bulb technology: LED
- Light colour: Cool white light
- Mains power: AC 220-240
- Fixture dimmable: No
- IP code: IP20
- Class of protection: Class I – Earthed

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8718696162811
- Net weight: 0.53 kg
- Gross weight: 0.99 kg
- Height: 41.8 cm
- Length: 8.9 cm
- Width: 41.8 cm



Issue date: 2026-05-25
Version: 0.400

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com