

Bulb

LED

40 W

E27

8718696167779



## Complete the classic look

This Philips classic cord combines a fabric wire and metal socket with classic finishing to bring a classic vibe to your living space. Paired with an E27 LED lamp from the Philips classic range to complete the look

### Designed for your living room and bedroom

- High quality material
- Adjustable cable length

### Choose a simple replacement for your old lamps

- Cord

# Highlights

## High quality material [Cable]

This beautiful fabric covered cable ensures that your lamp hangs straight when installed. The matt satin finish of the metal socket enhances the antique look of any bulb.

## Adjustable cable length [Cable]

Cable is fully adjustable for various heights giving the flexibility to arrange a stylish dynamic combination of suspension lighting above your kitchen island and dining table.

## Cord

This Philips lamp can be used in combination with one of the Philips cords to complete your interior illumination and bring an industrial feel to your living space.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Accessory
- Socket: E27
- Dimmable: No

## Durability

- Lumen maintenance factor: 70%
- Number of switch cycles: 25,000
- Nominal lifetime: 10,950

## Light characteristics

- Warm-up time to 60% light: Instant full light
- Luminous efficacy (rated) (nom.): 0.00 lm/W

## Miscellaneous

- Extra Features: Decorative

## Other characteristics

- Lamp current: 330 mA
- CE mark: Yes
- EU RoHS compliant: Yes

## Power consumption

- Power factor: 0.5
- Voltage: 120-240 V
- Power: 40 W

## Product dimensions and weight

- Length: 10.7 cm

## Rated values

- Rated power: 40 W

## Technical specifications

- Frequency: 50-60
- Line Frequency: 50 to 60
- Cap base: E27
- Can it be used in closed luminaires: No

## Packaging dimensions and weight

- EAN/UPC - product: 8718696167779
- Net weight: 0.43 kg
- Gross weight: 0.48 kg
- Height: 16.9 cm
- Length: 7.1 cm
- Width: 16.9 cm



Issue date: 2025-12-13  
Version: 0.1045

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)