

# PHILIPS

Spot 50W PAR16  
GU10 x6

LED

2700K

355 lm

15000 h

Non-dimmable



8718696586013



## Experience warm white LED light

This Philips LED light bulb provides a beautiful, extra warm light, an exceptionally long life and immediate, significant energy savings. With its flame colour temperature, this light bulb is the perfect choice for a cosy atmosphere.

### High-quality light

- True incandescent-like warm white light

### Choose a simple replacement for your old lamps

- Similar shape and size as halogen reflectors

### Create the right light for your home

- Perfect for accent lighting

# Highlights

## True incandescent-like warm white light



This bulb has a colour temperature of 2,700 K, providing you with a warm, tranquil atmosphere, perfect for relaxing. This 2,700 K light is ideal for home lighting design.

## Replaces halogen spots



With its beautifully shaped design and familiar dimensions, this is a modern lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

## Perfect for accent lighting



Modern lighting with a familiar wide-angle light output (36 degrees), this LED spot is suitable for both accent lighting and general-purpose lighting. It can be used in recesses and track light fixtures, and is ideal for use in kitchens, kitchen island lighting, living rooms and dining rooms.

# Specifications

## Bulb characteristics

- Shape: Spot
- Lamp shape: Directional reflector
- Socket: GU10
- Lamp Finish: Clear
- Dimmable: No
- Bulb material: Glass

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- LED integrated: Yes

## Light characteristics

- Beam angle: 36
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 355 lm
- Warm-up time to 60% light: 1
- Luminous efficacy (rated) (nom.): 77

## Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

## Packaging information

- Product family: LED Classic, EyeComfort

## Power consumption

- Power factor: 0.5
- Voltage: 220–240 V
- Wattage equivalent: 50
- Energy efficiency label (EEL): F
- Power: 4.6
- Energy consumption kWh/1,000 hours: 5

#### Product dimensions and weight

- Overall height: 54 mm
- Overall length: 54 mm
- Overall width: 50 mm

#### Rated values

- Rated peak intensity: 700 cd

#### Technical specifications

- Frequency: 50-60
- Bulb technology: LED
- EPREL Registration Number: 387358

#### The bulb

- Software upgradable: No

#### What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

#### Packaging dimensions and weight

- EAN/UPC - product: 8718696586013
- Net weight: 0.27 kg
- Gross weight: 0.34 kg
- Height: 11.5 cm
- Length: 5.3 cm
- Width: 17.1 cm



Issue date: 2026-05-13  
Version: 0.1233

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)