

# PHILIPS

## Halogen spot

Halogen Spot 12 V

50 W

GU5.3 cap

Warm white

Dimmable



8718696588789



## Stunning accent lighting

Philips halogen spots provide directional halogen light in natural, sparkling tones. This halogen lamp is designed to provide focused beams, creating bright accents in your home. It is fully dimmable.

### Superior light quality

- Cool beam for heat-sensitive objects
- Decorative accent lighting

### Dimmable

- Best dimmability to dim the light and create a cosy atmosphere

### The economical and ecological choice

- Double the lifetime of a traditional bulb

# Highlights

## Cool beam

The lower temperature in front of the Philips bulb, as compared to a normal reflector light bulb, minimises the effect of heat on sensitive objects.

## Decorative accent lighting



This Philips spot is designed to provide a focused, bright beam. Use it to highlight your special objects or combine multiple spots for general home lighting.

## Best dimmability

This lamp can be used in combination with all dimmers and will not only turn down the light to 0%, but also creates the cosy atmosphere you're used to from your incandescent.

## Double the lifetime



This lamp lasts twice as long as a standard bulb. So it replaces two lamps, for lower cost and less hassle. The lifetime is based on the average usage of 2.7 hrs per day or 1000 hrs a year.

# Specifications

## Bulb characteristics

- Lamp shape: Directional spot
- Socket: GU5.3
- Technology: Halogen
- Lamp shape code: MR16
- Dimmable: Yes

## Lamp dimensions

- Diameter: 51 mm
- Height: 46 mm
- Width: 51 mm

## Durability

- Average life (at 2.7 hrs/day): 4 year(s)
- Lumen maintenance factor: 0.8
- Number of switch cycles: 16,000
- Nominal lifetime: 4,000

## Light characteristics

- Application: Accent light
- Beam angle: 36 degree(s)
- Colour rendering index (CRI): 100
- Colour temperature: 3000 K
- Light Colour Category: Warm White
- Nominal luminous flux: 605 lm
- Starting time: 0 s
- Warm-up time to 60% light: Instant full light

## Power consumption

- Power factor: 1
- Voltage: 12 - 24 V
- Wattage: 50 W
- Energy consumption kWh/1,000 hours: 53

## Rated values

- Rated lifetime: 4,000
- Rated luminous flux: 680 lm
- Rated peak intensity: 1000 cd
- Rated power: 50 W

**Packaging dimensions and weight**

- EAN/UPC - product: 8718696588789
- Net weight: 0.06 kg
- Gross weight: 0.07 kg
- Height: 12 cm
- Length: 4.9 cm
- Width: 14 cm



Issue date: 2026-01-17  
Version: 0.795

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)