

PHILIPS

Filament Bulb Clear
60W A60 E27 x6

LED

2700K

806 lm

15000 h

Non-dimmable



8718696775059



A light bulb like no other

Familiar shapes you know and love. They provide you with the classic look of the incandescent lamps, while using around 80% less energy. The wide beam angle enables a perfect, all-around distribution of the light.

High-quality light

- Designed for the comfort of your eyes

Choose for a sustainable solution

- Saves up to 90% Energy

Create the right light for your home

- Perfect for general room lighting

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Saves up to 90% Energy



Enjoy the energy saving of LEDs without sacrificing light quality. Instantly save over 90% in energy by replacing your existing incandescent or halogen lamps

Perfect for general lighting



Modern lighting with Philips LED standard bulbs for all-around illumination, perfect for general room lighting.

Specifications

Bulb characteristics

- Shape: Bulb
- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: E27
- Dimmable: No
- Lamp Finish: Clear
- Bulb material: Glass

Lamp dimensions

- Height: 10.6 cm
- Width: 6 cm

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 806 lm
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

Other characteristics

- Efficacy: 115 lm/W

Packaging information

- Product family: LED Classic, EyeComfort
- EAN: 8718696775059
- EOC: 871869677505900
- Product title: LED classic 60W A60 E27 WW CL ND 6CT/4

Power consumption

- Power factor: 0.51
- Voltage: 220–240 V
- Wattage equivalent: 60 W
- Energy efficiency label (EEL): E
- Power Consumption: 7 W
- Energy consumption kWh/1,000 hours: 7

Product dimensions and weight

- Length: 10.4 cm

Technical specifications

- Frequency: 50–60 Hz
- EPREL Registration Number: 1825155

Packaging dimensions and weight

- EAN/UPC – product: 8718696775059
- Net weight: 0.18 kg
- Gross weight: 0.29 kg
- Height: 11.5 cm
- Length: 12.7 cm
- Width: 18.9 cm



Issue date: 2025-06-14
Version: 0.564

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com