

PHILIPS

Filament Bulb Clear
60W A60 E27 x3

LED

2700K

806 lm

15000 h



8718699719999



Experience warm white LED light

This Philips LED light bulb provides a beautiful, extra-warm light, an exceptionally long life and immediate, significant energy savings. With its flame colour temperature, this light bulb is the perfect choice for a cosy atmosphere.

High-quality light

- Designed for the comfort of your eyes

Choose for a sustainable solution

- Saves up to 90% Energy

Light beyond illumination

- Vintage style, modern LED technology

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up

your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Saves up to 90% Energy



Enjoy the energy saving of LEDs without sacrificing light quality. Instantly save over 90% in energy by replacing your existing incandescent or halogen lamps

Vintage-style, modern LED

LED Classic bulbs are based on standard LED energy-saving technology. Now you can enjoy a retro-style bulb with state-of-the-art technology combined with vintage design.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: E27
- Dimmable: No

Lamp dimensions

- Height: 10.6 cm
- Width: 6 cm

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 806 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 827 | CCT of 2700K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Efficacy: 115 lm/W

Packaging information

- EAN: 8718699719999
- EOC: 871869971999901
- Product title: LEDclassic 60W A60 E27 WW CL ND 3CT/4 UK

Power consumption

- Power factor: 0.51
- Voltage: 220–240 V
- Wattage: 7 W
- Wattage equivalent: 60 W
- Energy efficiency label (EEL): E
- Energy consumption kWh/1,000 hours: 7

Product dimensions and weight

- Length: 10.6 cm

Technical specifications

- Frequency: 50–60
- EPREL Registration Number: 1825155

Packaging dimensions and weight [LEDclassic 60W A60 E27 WW CL ND 3CT/4 UK]

- EAN/UPC - product: 8718699719999
- Net weight: 0.1 kg
- Gross weight: 0.16 kg
- Height: 12 cm
- Length: 7.6 cm
- Width: 21.7 cm

Packaging dimensions and weight [LED classic 60W A60 E27 WW CL ND 3CT/4]

- EAN/UPC - product: 8718699719999
- Net weight: 0.1 kg
- Gross weight: 0.16 kg
- Height: 12 cm
- Length: 7.6 cm
- Width: 21.7 cm



Issue date: 2025-11-15
Version: 0.250

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com