

PHILIPS

Bulb 60;30; 16 W
A60 E27

LED

2700/2500/2200K

806;320;150 lm

15000 h



8718699772130



One lamp. Your switch. Three light settings.

Change your room ambiance to suit whatever you're doing. With the Philips SceneSwitch LED lamp, you can easily change the setting from bright light, to natural light and to a cosy warm glow. All you need is your existing switch.

Light beyond illumination

- Three light settings
- No dimmer or additional installation needed

High-quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

Three light settings (SSDL)

All-in one replacement bulb that changes between three different brightness levels of Daylight, all with your existing switch.

Plug and play



Does not require any additional installation or a dimmer switch. This lamp is not suitable for use with dimmers. If used on a dimmer setting, the dimmer is set to 100% brightness.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: E27
- Dimmable: No
- Lamp Finish: Clear
- Bulb material: Glass

Lamp dimensions

- Height: 10.4 cm
- Width: 6 cm

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 h

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700/2500/2200 K
- Nominal luminous flux: 806, 320, 150 lm
- Warm-up time to 60% light: 0.5 s
- Colour Code: 827/825/822 | CCT of 2700K/2500K/2200K
- Correlated Colour Temperature (Nom): 2700, 2500, 2200 K
- Stroboscopic effect: 0.4
- Luminous efficacy (rated) (nom.): 107.00 lm/W

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: SceneSwitch

Other characteristics

- Efficacy: 107 lm/W
- CE mark: Yes
- EU RoHS compliant: Yes

Packaging information

- EAN: 8718699772130
- EOC: 871869977213001
- Product title: LEDClassic SSW 60W A60 E27WWCLND RF1SRT4

Power

- Power Factor (Fraction): 0.5

Power consumption

- Power factor: 0.5
- Voltage: AC 220-240 V
- Wattage: 7.5, 3, 1.6 W
- Wattage equivalent: 60;30;16 W
- Power Consumption: 1.6, 3, 7.5 W
- Energy efficiency label (EEL): F

Product dimensions and weight

- Length: 10.4 cm

Rated values

- Rated lifetime: 15,000 h

Technical specifications

- Frequency: 50-60 Hz
- EPREL Registration Number: 739280
- Flux measurement reference: Sphere
- Flickering value (PstLM): 0.9
- Line Frequency: 50 to 60 Hz
- Dimmable: No
- Cap base: E27

Packaging dimensions and weight

- EAN/UPC – product: 8718699772130
- Net weight: 0.07 kg
- Gross weight: 0.1 kg
- Height: 14.6 cm
- Length: 6.5 cm
- Width: 6.3 cm



Issue date: 2025-04-09
Version: 0.362

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com