

# PHILIPS

Spot 50W MR16  
GU5.3

LED

2200-2700K

621 lm

15000 h

Dimming



8718699774035



## The right light makes the moment

The Philips LED WarmGlow lamps offer a new experience for dimmable LEDs, by enabling light levels to dim to the warm tones of traditional lamps. You can change the ambience from functional lighting to an inviting and cosy atmosphere.

### High-quality light

- True incandescent-like warm white light

# Highlights

## Incandescent-like warm white

This bulb has a colour temperature of 2,700 K, providing you with a warm,

tranquil atmosphere, perfect for relaxing. Ideal for home lighting design

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional spot
- Socket: GU5.3
- Lamp Finish: Clear
- Dimmable: Yes
- Bulb material: Glass

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- LED integrated: Yes

## Light characteristics

- Beam angle: 36
- Colour rendering index (CRI): 80
- Colour temperature: 2200-2700 K
- Nominal luminous flux: 621 lm
- Warm-up time to 60% light: 0.5
- Colour Code: 822-827 | tunable warm white
- Luminous efficacy (rated) (nom.): 88

## Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Dimmable, WarmGlow

## Packaging information

- EAN: 8718699774035
- EOC: 871869977403500
- Product title: LED 50W GU5.3 WW 12V 36D WGD SRT4

## Power consumption

- Power factor: 0.85
- Voltage: 12V AC electronic V
- Wattage equivalent: 50
- Energy efficiency label (EEL): F
- Power: 7
- Energy consumption kWh/1,000 hours: 7

## Product dimensions and weight

- Overall height: 46 mm
- Overall length: 45.5 mm
- Overall width: 51 mm

## Rated values

- Rated peak intensity: 1000 cd

## Technical specifications

- Frequency: 50-60
- Bulb technology: LED
- EPREL Registration Number: 391904

## The bulb

- Software upgradable: No

## What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

8718699774035

**Packaging dimensions and weight**

- EAN/UPC - product: 8718699774035
- Net weight: 0.05 kg
- Gross weight: 0.07 kg
- Height: 12.7 cm
- Length: 5.3 cm
- Width: 6.3 cm



Issue date: 2026-04-15  
Version: 0.257

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)