

PHILIPS

Capsule 60 W
Capsule G9

LED

2700K

570 lm

15000 h



8718699774073



Warm white light, with excellent light quality

Philips LEDspots are a perfect fit for your basic lighting needs: they deliver warm halogen-like light and deliver the performance you expect from the LED technology.

High-quality light

- True incandescent-like warm white light

Choose a simple replacement for your old lamps

- Shape and size similar to halogen capsules

Choose for a sustainable solution

- Long-life tubes – Lasts up to 15 years
- Saves up to 90% Energy

Highlights

True incandescent-like warm white light



This bulb has a colour temperature of 2,700 K, providing you with a warm, tranquil atmosphere, perfect for relaxing. This 2,700 K light is ideal for home lighting design.

Replaces halogen capsules



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting LED capsule. The perfect sustainable replacement for traditional halogen capsules.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light tubes and enjoy a perfect lighting solution for over 15 years.

Saves up to 90% Energy



Enjoy the energy saving of LEDs without sacrificing light quality. Instantly save over 90% in energy by replacing your existing incandescent or halogen lamps

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional capsule
- Socket: G9
- Dimmable: No
- Lamp Finish: Clear
- Bulb material: Plastic

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 570 lm
- Warm-up time to 60% light: 0.4
- Colour Code: 827 | CCT of 2700K
- Luminous efficacy (rated) (nom.): 118 lm/W

Miscellaneous

- EyeComfort: No

Packaging information

- EAN: 8718699774073
- EOC: 871869977407300
- Product title: LED 60W G9 WW ND SRT6

Power consumption

- Power factor: 0.4
- Voltage: 220–240 V
- Wattage equivalent: 60 W
- Energy efficiency label (EEL): E
- Power: 4.8 W
- Energy consumption kWh/1,000 hours: 5

Product dimensions and weight

- Overall height: 60 mm
- Overall length: 60 mm
- Overall width: 19 mm

Technical specifications

- Frequency: 50–60
- EPREL Registration Number: 397599

Packaging dimensions and weight

- EAN/UPC – product: 8718699774073
- Net weight: 0.01 kg
- Gross weight: 0.02 kg
- Height: 12.7 cm
- Length: 2.5 cm
- Width: 6.3 cm



Issue date: 2026-01-31
Version: 0.180

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com