

# PHILIPS

Spot 80W PAR16  
GU10

LED

2200-2700K

575 lm

25000 h

Dimming



8718699774097



## The right light makes the moment

The Philips LED WarmGlow lamps offer a new experience for dimmable LEDs, by enabling light levels to dim to the warm tones of traditional lamps. You can change the ambience from functional lighting to an inviting and cosy atmosphere.

### High-quality light

- True incandescent-like warm white light

### Light beyond illumination

- Dimmable

# Highlights

## Incandescent-like warm white

This bulb has a colour temperature of 2,700 K, providing you with a warm, tranquil atmosphere, perfect for relaxing. Ideal for home lighting design

## Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be

certain that your particular dimmer can be used with this bulb.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Dimmable: Yes
- Lamp Finish: Clear
- Bulb material: Glass

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 25,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 36 degree(s)
- Colour rendering index (CRI): 90
- Colour temperature: 2200-2700 K
- Nominal luminous flux: 575 lm
- Warm-up time to 60% light: 0.5
- Colour Code: 922-927 | CCT of 2200K-2700K
- Luminous efficacy (rated) (nom.): 92 lm/W

## Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Dimmable, WarmGlow

## Packaging information

- EAN: 8718699774097
- EOC: 871869977409700
- Product title: LED CLA 80W GU10 CRI90 WW 36D WGD SRT4

## Power consumption

- Power factor: 0.88
- Voltage: 220-240 V
- Wattage equivalent: 80 W
- Energy efficiency label (EEL): F
- Power Consumption: 6.2 W
- Energy consumption kWh/1,000 hours: 7

## Product dimensions and weight

- Overall height: 56 mm
- Overall length: 56 mm
- Overall width: 50 mm

## Rated values

- Rated peak intensity: 950 cd

## Technical specifications

- Frequency: 50-60
- EPREL Registration Number: 387456

## Packaging dimensions and weight

- EAN/UPC – product: 8718699774097
- Net weight: 0.05 kg
- Gross weight: 0.07 kg
- Height: 12.7 cm
- Length: 5.3 cm
- Width: 6.3 cm



Issue date: 2025-11-19  
Version: 0.260

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)