

PHILIPS

Spot 120W R7S R7S

LED

14 W-120 W


R7S

Cool White

Dimming



8718699776039



Dimmable linear LED light with a 300-degree beam

This innovative Linear LED is the perfect replacement for halogen R7S bulbs, while far surpassing them in terms of energy efficiency.

High-quality light

- Cool, white light

Choose a simple replacement for your old lamps

- Shape and size similar to halogen spot
- Similar shape and size as halogen linears

Highlights

Cool, white light



This lamp has a colour temperature of 4000K providing you with an extra cool, fresh and crisp light.

Replaces halogen reflector



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, LED capsule. The perfect sustainable replacement for traditional halogen spots.

Replaces linear halogens



With its beautifully shaped design and familiar dimensions, this standard modern lighting, LED linear is the perfect sustainable replacement for traditional halogen linears.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional reflector
- Socket: R7s
- Dimmable: Yes

Lamp dimensions

- Height: 11.8 cm
- Width: 2.9 cm

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Nominal luminous flux: 2000 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 840 | CCT of 4000K

Miscellaneous

- EyeComfort: No

Other characteristics

- Efficacy: 142 lm/W

Packaging information

- EAN: 8718699776039
- EOC: 871869977603900
- Product title: LED 120W R7S 118mm CW D 1PF/12

Power consumption

- Power factor: 0.8
- Voltage: 220-240 V
- Wattage: 14 W
- Wattage equivalent: 120 W
- Energy efficiency label (EEL): D
- Energy consumption kWh/1,000 hours: 14

Product dimensions and weight

- Length: 11.8 cm

Technical specifications

- Frequency: 50-60
- EPREL Registration Number: 397583

Packaging dimensions and weight [LED 120W R7S 118mm CW D 1PF SRT4]

- EAN/UPC – product: 8718699776039
- Net weight: 0.14 kg
- Gross weight: 0.17 kg
- Height: 14.6 cm
- Length: 3 cm
- Width: 6.3 cm

Packaging dimensions and weight

[LED 120W R7S 118mm CW D 1PF/12]

- EAN/UPC – product: 8718699776039
- Net weight: 0.09 kg
- Gross weight: 0.11 kg
- Height: 14.6 cm
- Length: 3 cm
- Width: 6.3 cm



Issue date: 2025-11-01
Version: 0.285

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com