

PHILIPS

Spot 35 W PAR16
GU10 x3

LED

4000K

275 lm

15000 h



8718699776251



Experience warm white LED light

This Philips LED light bulb provides a beautiful, extra-warm light, an exceptionally long life and immediate, significant energy savings. With its flame colour temperature, this light bulb is the perfect choice for a cosy atmosphere.

High-quality light

- Cool, white light

Choose a simple replacement for your old lamps

- Similar shape and size as halogen reflectors

Create the right light for your home

- Perfect for accent lighting

Highlights

Cool, white light



This lamp has a colour temperature of 4000K providing you with an extra cool, fresh and crisp light.

Replaces halogen spots



With its beautifully shaped design and familiar dimensions, this is a modern lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

Perfect for accent lighting



Modern lighting with a familiar wide-angle light output (36 degrees), this LED spot is suitable for both accent lighting and general-purpose lighting. It can be used in recesses and track light fixtures, and is ideal for use in kitchens, kitchen island lighting, living rooms and dining rooms.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Lamp Finish: Clear
- Dimmable: No
- Bulb material: Glass

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Beam angle: 36
- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Nominal luminous flux: 275 lm
- Warm-up time to 60% light: 0.5
- Colour Code: 840 | CCT of 4000K
- Luminous efficacy (rated) (nom.): 78

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

Packaging information

- EAN: 8718699776251
- EOC: 871869977625100
- Product title: LEDClassic 35W GU10 CW 230V 36D ND 3SRT6

Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage equivalent: 35
- Energy efficiency label (EEL): F
- Power: 3.5
- Energy consumption kWh/1,000 hours: 4

Product dimensions and weight

- Overall height: 54 mm
- Overall length: 54 mm
- Overall width: 50 mm

Rated values

- Rated peak intensity: 590 cd

Technical specifications

- Frequency: 50-60
- Bulb technology: LED
- EPREL Registration Number: 391857

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8718699776251
- Net weight: 0.14 kg
- Gross weight: 0.17 kg
- Height: 12.7 cm
- Length: 5.3 cm
- Width: 11.5 cm



Issue date: 2026-05-13
Version: 0.136

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com