

# PHILIPS

Spot 50 W PAR16  
GU10 x3

LED

4000K

390 lm

15000 h



8718699776312



## Experience warm white LED light

This Philips LED light bulb provides a beautiful, extra-warm light, an exceptionally long life and immediate, significant energy savings. With its flame colour temperature, this light bulb is the perfect choice for a cosy atmosphere.

### High-quality light

- Cool, white light

### Choose a simple replacement for your old lamps

- Similar shape and size as halogen reflectors

### Create the right light for your home

- Perfect for accent lighting

# Highlights

## Cool, white light



This lamp has a colour temperature of 4000K providing you with an extra cool, fresh and crisp light.

## Replaces halogen spots



With its beautifully shaped design and familiar dimensions, this is a modern lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

## Perfect for accent lighting



Modern lighting with a familiar wide-angle light output (36 degrees), this LED spot is suitable for both accent lighting and general-purpose lighting. It can be used in recesses and track light fixtures, and is ideal for use in kitchens, kitchen island lighting, living rooms and dining rooms.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Lamp Finish: Clear
- Dimmable: No
- Bulb material: Glass

## Lamp dimensions

- Height: 5.4 cm
- Width: 5 cm

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 h

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 36 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Nominal luminous flux: 390 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 840 | CCT of 4000K

## Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

## Other characteristics

- Efficacy: 84 lm/W

## Packaging information

- EAN: 8718699776312
- EOC: 871869977631200
- Product title: LEDClassic 50W GU10 CW 36D ND 3SRT6

## Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 4.6 W
- Wattage equivalent: 50 W
- Energy efficiency label (EEL): F

#### Product dimensions and weight

- Length: 5.4 cm

#### Rated values

- Rated peak intensity: 770 cd

#### Technical specifications

- Frequency: 50-60 Hz
- EPREL Registration Number: 391859

#### Packaging dimensions and weight

- EAN/UPC – product: 8718699776312
- Net weight: 0.14 kg
- Gross weight: 0.17 kg
- Height: 12.7 cm
- Length: 5.3 cm
- Width: 11.5 cm



Issue date: 2025-04-19  
Version: 0.197

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)