

# PHILIPS

Spot 35W PAR16  
GU10 x3

LED

2.6 W-35 W

GU10

Warm Glow

Dimming



8718699776411



## The more you dim, the warmer the light.

Philips WarmGlow LEDs let you dim your everyday light down to the cosy tones of traditional lamps. So the more you dim, the warmer the light appears. This sets them apart from standard dimmable LEDs, which simply get less bright when dimmed. WarmGlow lamps are now also enhanced with a Colour Rendering Index of 90, which is comparable to natural light, helping you see your home's true colours. Whether you're getting cosy on the sofa in the evening, or looking for a bright start to your day, Philips WarmGlow LEDs have the right light to suit your needs.

### High-quality light

- True incandescent-like warm white light

### Create the right light for your home

- Perfect for accent lighting

# Highlights

## Incandescent-like warm white

This bulb has a colour temperature of 2,700 K, providing you with a warm, tranquil atmosphere, perfect for relaxing. Ideal for home lighting design

## Perfect for accent lighting



Modern lighting with a familiar wide-angle light output (36 degrees), this LED spot is suitable for both accent lighting and general-purpose lighting. It can be used in recesses and track light fixtures, and is ideal for use in kitchens, kitchen island lighting, living rooms and dining rooms.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Dimmable: Yes
- Lamp Finish: Clear
- Bulb material: Glass

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 36 degree(s)
- Colour rendering index (CRI): 90
- Colour temperature: 2200-2700 K
- Nominal luminous flux: 230 lm
- Warm-up time to 60% light: 0.5
- Colour Code: 922-927 | CCT of 2200K-2700K
- Luminous efficacy (rated) (nom.): 88 lm/W

## Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Dimmable, WarmGlow

## Packaging information

- EAN: 8718699776411
- EOC: 871869977641100
- Product title: LED CLA 35W GU10 C90 WW 36D WGD 3SRT6

## Power consumption

- Power factor: 0.8
- Voltage: 220-240 V
- Wattage equivalent: 35 W
- Energy efficiency label (EEL): F
- Power Consumption: 2.6 W
- Energy consumption kWh/1,000 hours: 3

## Product dimensions and weight

- Overall height: 54 mm
- Overall length: 54 mm
- Overall width: 50 mm

## Rated values

- Rated peak intensity: 500 cd

## Technical specifications

- Frequency: 50-60
- EPREL Registration Number: 387454

8718699776411

**Packaging dimensions and weight**

- EAN/UPC - product: 8718699776411
- Net weight: 0.14 kg
- Gross weight: 0.17 kg
- Height: 12.7 cm
- Length: 5.3 cm
- Width: 11.5 cm



Issue date: 2025-11-12  
Version: 0.191

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)