

# PHILIPS

Spot

LED

3.5W-35W

GU10

Cool White



8718699776534



## Experience warm white LED light

This Philips LED light bulb provides a beautiful, extra-warm light, an exceptionally long life and immediate, significant energy savings. With its flame colour temperature, this light bulb is the perfect choice for a cosy atmosphere.

### High-quality light

- Cool, white light

### Choose a simple replacement for your old lamps

- Similar shape and size as halogen reflectors

### Create the right light for your home

- Perfect for accent lighting

# Highlights

## Cool, white light



This lamp has a colour temperature of 4000K providing you with an extra cool, fresh and crisp light.

## Replaces halogen spots



With its beautifully shaped design and familiar dimensions, this is a modern lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

## Perfect for accent lighting



Modern lighting with a familiar wide-angle light output (36 degrees), this LED spot is suitable for both accent lighting and general-purpose lighting. It can be used in recesses and track light fixtures, and is ideal for use in kitchens, kitchen island lighting, living rooms and dining rooms.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Lamp Finish: Clear
- Dimmable: No
- Bulb material: Glass

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- LED integrated: Yes

## Light characteristics

- Beam angle: 36
- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Nominal luminous flux: 275 lm
- Warm-up time to 60% light: 0.5
- Colour Code: 840 | CCT of 4000K
- Luminous efficacy (rated) (nom.): 78

## Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

## Packaging information

- EAN: 8718699776534
- EOC: 871869977653401
- Product title: LEDClassic 35W GU10 CW 36D ND 1PF SRT4

## Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage equivalent: 35
- Energy efficiency label (EEL): F
- Power: 3.5
- Energy consumption kWh/1,000 hours: 4

#### Product dimensions and weight

- Overall height: 54 mm
- Overall length: 54 mm
- Overall width: 50 mm

#### Rated values

- Rated peak intensity: 590 cd

#### Technical specifications

- Frequency: 50-60
- Bulb technology: LED
- EPREL Registration Number: 391857

#### Packaging dimensions and weight

- EAN/UPC - product: 8718699776534
- Net weight: 0.05 kg
- Gross weight: 0.07 kg
- Height: 12.7 cm
- Length: 5.3 cm
- Width: 6.3 cm



Issue date: 2026-03-31  
Version: 0.408

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)