

# PHILIPS

Bulb 60 W A19 E27

LED

2700K

806 lm

15000 h



8718699782696



## Dusk to dawn

The Philips LED Dusk to Dawn bulb is designed to save even more energy than regular LED by turning itself on and off with the level of daylight – providing secure light during the night, and turning off with the light of day.

### Light beyond illumination

- Built-in automatic on/off light sensor

### High-quality LED light that lasts for decades

- Designed for the comfort of your eyes

# Highlights

## Day and night sensor



With its built-in automatic light sensor, this bulb switches on automatically after dusk and off after dawn.

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright and you get glare. Too soft and you experience flicker. Now you can gently light up

your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: E27
- Dimmable: No
- Lamp Finish: Frosted
- Bulb material: Plastic

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Guarantee

- Warranty period: 2 years

## Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 806 lm
- Warm-up time to 60% light: 0.5 s
- Colour Code: 827 | CCT of 2700K
- Correlated Colour Temperature (Nom): 2700 K
- Luminous Flux: 806 lm
- Stroboscopic effect: 0.4
- Luminous efficacy (rated) (nom.): 107.00 lm/W

## Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

## Other characteristics

- EU RoHS compliant: Yes

## Packaging information

- EAN: 8718699782696
- EOC: 871869978269600
- Product title: LED D2D 60W A60 E27 WW FR ND SRT4

## Power

- Power Factor (Fraction): 0.7

**Power consumption**

- Power factor: 0.7
- Voltage: 230 V
- Wattage equivalent: 60 W
- Energy efficiency label (EEL): F
- Power Consumption: 7.5 W
- Energy consumption kWh/1,000 hours: 8

**Product dimensions and weight**

- Overall height: 114 mm
- Overall length: 114 mm
- Overall width: 62 mm

**Rated values**

- Rated lifetime: 15,000

**Technical specifications**

- Frequency: 50
- Diameter: 62 mm
- EPREL Registration Number: 391894
- Flux measurement reference: Sphere
- Dimmable: No
- Flickering value (PstLM): 1
- Line Frequency: 50
- Cap base: E27

**Packaging dimensions and weight**

- EAN/UPC – product: 8718699782696
- Net weight: 0.06 kg
- Gross weight: 0.1 kg
- Height: 14.6 cm
- Length: 6.5 cm
- Width: 6.3 cm



Issue date: 2025-08-30  
Version: 0.268

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)