

PHILIPS

Filament Candle
Clear 25W T25 E14

LED

2.1W-25W

E14

Warm White



8718699783334



Experience warm white LED light

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

High-quality light

- Designed for the comfort of your eyes

Choose a simple replacement for your old lamps

- Similar shape and size as standard incandescent bulbs

Choose for a sustainable solution

- Long-life bulbs – Last up to 15 years

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Replaces standard incandescents



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect sustainable replacement for traditional standard incandescent bulbs.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional lustre
- Socket: E14
- Type of glass: Clear
- Dimmable: No
- Lamp Finish: Clear
- Bulb material: Glass

Lamp dimensions

- Height: 8.5 cm
- Width: 2.5 cm

Design and finishing

- Material: Glass

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000
- Ambient temperature range: -20 to +45 °C

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 250 lm
- Warm-up time to 60% light: 0.5 s
- Colour Code: 827 | CCT of 2700K
- Correlated Colour Temperature (Nom): 2700 K
- Luminous Flux: 250 lm
- Stroboscopic effect: 0.4
- Luminous efficacy (rated) (nom.): 119 lm/W

Other characteristics

- Efficacy: 119 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 8718699783334
- EOC: 871869978333402
- Product title: LED classic 25W T25L E14 CL ND RF SRT4

Power

- Power Factor (Fraction): 0.41

Power consumption

- Power factor: 0.41
- Voltage: 230 V
- Wattage equivalent: 25 W
- Energy efficiency label (EEL): E
- Power Consumption: 2.1 W
- Energy consumption kWh/1,000 hours: 3

Product dimensions and weight

- Length: 8.5 cm

Technical specifications

- Frequency: 50-60
- Diameter: 25 mm
- EPREL Registration Number: 374879
- Flux measurement reference: Sphere
- Dimmable: No
- Flickering value (PstLM): 1
- Cap base: E14

Packaging dimensions and weight

- EAN/UPC – product: 8718699783334
- Net weight: 0.01 kg
- Gross weight: 0.03 kg
- Height: 12.7 cm
- Length: 4.6 cm
- Width: 6.3 cm



Issue date: 2025-06-21
Version: 0.250

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com