




Bulb 100W A67 E27



Colour, colour, colour, colour, colour chameleon! Don't let the standard A67 shape fool you: there's nothing standard about the light that comes out of these large-format LED powerhouses. Choose from millions of colours to match whatever you've got going on – whether it's a rollicking party, an elegant dinner or chilling on the couch with a good movie – or create schedules to automatically transition to the perfect ambiance as your needs and moods change. All Wi-Fi controllable using the WiZ app, WiZ remote or even your voice.


PRODUCT HIGHLIGHTS

- Full colour smart bulb
- Up to 1521 lumens
- Easy plug and play
- Control with app or voice




Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and get the lights to turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.




Monitor your energy consumption

Get an overview of the energy consumption of your lights with the WiZ app. Easily access a weekly or daily report to help you stay on top of your energy consumption at home.



Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



Create your perfect light scene

Make your own mix of different colour and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.



Millions of colours and changing light modes to make your day

Choose any light colour you like or simply apply a dynamic light mode that we've designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Lamp shape: A67
Socket: E27
Type of glass: Frosted
Dimmable: Yes

LAMP DIMENSIONS

Weight: 0.108 kg

DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 15,000

LIGHT CHARACTERISTICS

Colour consistency: 6 SDCM
Colour rendering index (CRI): ≥ 90
Colour temperature: 2200-6500 K
Light Colour Category: Full colour
Nominal luminous flux: 1521 lm
Starting time: < 0.5 s
Warm-up time to 60% light: Instant full light
Luminous efficacy (rated) (nom.): 117 lm/W

OTHER CHARACTERISTICS

Lamp current: 110 mA

PACKAGING INFORMATION

EAN: 8718699786199
EOC: 871869978619901
Product title: Wi-Fi BLE 100W A67 E27
922-65 RGB 1PF/6

POWER CONSUMPTION

Power factor: 0.55
Voltage: 220-240 V
Wattage equivalent: 100 W
Energy efficiency label (EEL): E
Power Consumption: 13 W
Energy consumption kWh/1,000 hours: 13

PRODUCT DIMENSIONS AND WEIGHT

Overall height: 142 mm
Overall length: 142 mm
Overall width: 77 mm

RATED VALUES

Rated lifetime: 15,000
Rated luminous flux: 1521 lm
Rated power: 13 W

TECHNICAL SPECIFICATIONS

Frequency: 50-60
EPREL Registration Number: 1901113
Flux measurement reference: Sphere

WHAT'S SUPPORTED

Compatible with Effects feature: Yes
WiFi: Wireless G
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth
WiFi (2.4GHz)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8718699786199
Net weight: 0.08 kg
Gross weight: 0.12 kg
Height: 18.5 cm
Length: 8.5 cm
Width: 8.5 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.