



# Filament Bulb Amber 25 W PS160 E27



An amber coating and shades of warm or cool white light let you set the mood with this elongated WiZ vintage-style tunable white smart Filament bulb. Use with the WiZ app or your voice to dim and brighten or use preset light modes on Wi-Fi setups.

## PRODUCT HIGHLIGHTS

- Tunable white smart bulb
- Up to 390 lumens
- Easy plug and play
- Control with app or voice



### Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



### Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



### Create your perfect light scene

Make your own mix of different colour and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.



### Set the right ambience with tunable warm to cool white light

Choose from a wide range of energising cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



### Dim your smart lights even without a dimmer

Simply adjust lights to your desired brightness level using your smartphone, the WiZ control accessory or just your voice. No need to install an expensive dimmer!



### Control smart lighting the way you like it

WiZ enables you to control smart lighting in multiple ways. Adjust lights with your smartphone, voice, the WiZ remote control or by using the existing wall switch to toggle between two favourite modes. Works with Google Home, Alexa and Siri Shortcuts.



# SPECIFICATIONS

## BULB CHARACTERISTICS

Intended use: Indoor  
Lamp shape: PS160  
Socket: E27  
Type of glass: Amber  
Dimmable: Yes

## LAMP DIMENSIONS

Weight: 0.275 kg

## DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)  
Lumen maintenance factor: 70%  
Number of switch cycles: 20,000  
Nominal lifetime: 15,000

## LIGHT CHARACTERISTICS

Colour consistency: 6 SDCM  
Colour rendering index (CRI):  $\geq 90$   
Colour temperature: 2000-5000 K  
Light Colour Category: Tunable white  
Nominal luminous flux: 390 lm  
Starting time:  $< 0.5$  s  
Warm-up time to 60% light: Instant full light  
Luminous efficacy (rated) (nom.): 65 lm/W

## OTHER CHARACTERISTICS

Lamp current: 39 mA

## PACKAGING INFORMATION

EAN: 8718699786854  
EOC: 871869978685401  
Product title: Wi-Fi BLE 25W PS160  
E27 920-50 Amb 1CT/2

## POWER CONSUMPTION

Power factor: 0.5  
Voltage: 220-240 V  
Wattage equivalent: 25 W  
Energy efficiency label (EEL): G  
Power Consumption: 6 W  
Energy consumption kWh/1,000 hours: 6

## PRODUCT DIMENSIONS AND WEIGHT

Overall height: 296 mm  
Overall length: 296 mm  
Overall width: 160 mm

## RATED VALUES

Rated lifetime: 15,000  
Rated luminous flux: 390 lm  
Rated power: 6 W

## SERVICE

Warranty: 2 year(s)

## TECHNICAL SPECIFICATIONS

Frequency: 50-60  
EPREL Registration Number: 1901142  
Flux measurement reference: Sphere

## WHAT'S SUPPORTED

Compatible with Effects feature: Yes  
WiFi: Wireless G  
Defined support period: Minimum of 60 months after introduction date  
Max. number of accessories: 9999  
Communication protocol: Bluetooth  
WiFi (2.4GHz)

## PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8718699786854  
Net weight: 0.28 kg  
Gross weight: 0.49 kg  
Height: 32 cm  
Length: 18.5 cm  
Width: 18.5 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.