




Candle 40 W C37 E14



Who doesn't love the look of a candle? These energy-friendly candle-shape LED bulbs give you all the elegance of candlelight along with something that no standard candle could ever do: hundreds of shades of white light that you can tune to match your ever-changing needs and moods. Schedule cool light when you need to focus or cosy light when you want to relax –whatever works for you to live your best, most enjoyable life at home. All Wi-Fi controllable using the WiZ app, WiZ remote or your voice.

PRODUCT HIGHLIGHTS

- Tunable white smart bulb
- Up to 470 lumens
- Easy plug and play
- Control with app or voice




Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and get the lights to turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.




Monitor your energy consumption

Get an overview of the energy consumption of your lights with the WiZ app. Easily access a weekly or daily report to help you stay on top of your energy consumption at home.



Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



Create your perfect light scene

Make your own mix of different colour and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energising cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Lamp shape: C37
Socket: E14
Technology: Smart Wi-Fi
Type of glass: Frosted
Dimmable: Yes

LAMP DIMENSIONS

Height: 11.6 cm
Weight: 0.045 kg
Width: 3.9 cm

DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 15,000

LIGHT CHARACTERISTICS

Colour consistency: 6 SDCM
Colour rendering index (CRI): ≥ 90
Colour temperature: 2700-6500 K
Light Colour Category: Tunable white
Nominal luminous flux: 470 lm
Starting time: < 0.5 s
Warm-up time to 60% light: Instant full light

OTHER CHARACTERISTICS

Lamp current: 40 mA
Efficacy: 95 lm/W

PACKAGING INFORMATION

EAN: 8718699787073
EOC: 871869978707301
Product title: Wi-Fi BLE 40W C37 E14
927-65 TW 1PF/6

POWER CONSUMPTION

Power factor: 0.51
Voltage: 220-240 V
Wattage: 4.9 W
Wattage equivalent: 40 W
Energy efficiency label (EEL): F

PRODUCT DIMENSIONS AND WEIGHT

Length: 11.6 cm

RATED VALUES

Rated lifetime: 15,000
Rated luminous flux: 470 lm
Rated power: 4.9 W

TECHNICAL SPECIFICATIONS

Frequency: 50-60 Hz
EPREL Registration Number: 1901096
Flux measurement reference: Sphere

THE BRIDGE

Max. number of accessories: 9,999

THE BULB

Communication protocol: Bluetooth
WiFi (2.4GHz)

WHAT'S SUPPORTED

Compatible with Effects feature: Yes
WiFi: Wireless G
Defined support period: Minimum of 60 months after introduction date

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8718699787073
Net weight: 0.05 kg
Gross weight: 0.09 kg
Height: 16 cm
Length: 7 cm
Width: 7 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.