

# PHILIPS

## Abrosa Recessed Light 9W

Recessed Lights

2700K

White

Dimmable; Water Resistant



8719514254596



## Create the perfect ambience with high-quality dimmable light.

Create the perfect mood with Philips LED Dimmable recessed spots, you can easily dim your lights from everyday bright light to cosy tones.

### Easy to experience

- Choose how and where light falls with these adjustable modular lights.

### Light effect

- Bright and focused beam

### Safety

- Moisture resistance

### Premium quality

- EyeComfort – light that's easy on the eyes

### Control

- Dimmable

### Durability

- Long life span up to 25,000 hours

# Highlights

## Adjustable modular light

### Bright and focused beam

Focus light on objects, a dining table or other interiors to draw attention to particular stylings.

### Moisture resistance

Moisture resistance means you can confidently use this product in bathrooms, kitchens, balconies and other spaces where moisture may be a consideration.

## EyeComfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, colour rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output and

colour for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

### Dimmable

Allows you to change the mood by reducing LED brightness levels, from bright white light to a cosy glow – just like traditional lamps.

### Long life span up to 25,000 hours

Philips LED technology extends your product's lifetime up to 25,000 hours

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Colour: White
- Material: Metal

## Durability

- Number of switch cycles: 12,500
- Nominal lifetime: 25,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Beam angle: 38 degree(s)
- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Luminous efficacy (rated) (nom.): 72 lm/W

## Miscellaneous

- Especially designed for: Bathroom, Bedroom, Living Room, Dining Room, Kitchen, Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes
- Extra Features: Dimmable, Water Resistant

## Other characteristics

- Lamp current: 43 mA

## Product dimensions and weight

- Net weight: 0.17 kg
- Recessed distance: 100 mm
- Overall height: 62 mm
- Overall length: 86 mm
- Overall width: 86 mm
- Recessed ceiling cutout: 6.8 cm x 6.8 cm

## Service

- Warranty: 2 year(s)

**Technical specifications**

- Diameter: 86 mm
- Total lumen output fixture: 700
- Light colour: Warm white light
- Mains power: AC 220-240
- Fixture dimmable: Yes
- Wattage bulb included: 9
- IP code: IP20 | Finger-protected, IP44  
| Wire-protected and splash-proof
- Class of protection: Class II – Double Insulated

**Packaging dimensions and weight**

- EAN/UPC – product: 8719514254596
- Net weight: 0.17 kg
- Gross weight: 0.21 kg
- Height: 8.5 cm
- Length: 10 cm
- Width: 10 cm



Issue date: 2025-12-24  
Version: 0.365

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)