

# PHILIPS

Filament Bulb Pink  
25W ST19 E27

LED

1800 K


250 lm

15000 h

Dimming



8719514269538



## A light bulb like no other

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

### Light beyond illumination

- Vintage style, modern LED technology

### High-quality LED light that lasts for decades

- Designed for the comfort of your eyes

### Designed to be seen, looks good on and off

- Looks good on and off

# Highlights

## Vintage-style, modern LED

LED Classic bulbs are based on standard LED energy-saving technology. Now you can enjoy a retro-style bulb with state-of-the-art technology combined with vintage design.

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Looks good on and off



"These beautiful lamp with visible filament add a sense of style and nostalgia to any room. Looks good on and off."

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: E27
- Lamp Finish: Pink
- Dimmable: Yes
- Bulb material: Glass

## Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

**Light characteristics**

- Colour rendering index (CRI): 80
- Colour temperature: 1800 K
- Nominal luminous flux: 250 lm
- Warm-up time to 60% light: 0.5 s
- Colour Code: 818 | CCT of 1800K
- Correlated Colour Temperature (Nom): 1800 K
- Luminous Flux: 250 lm
- Stroboscopic effect: 0.4
- Luminous efficacy (rated) (nom.): 55.00 lm/W

**Miscellaneous**

- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Dimmable, Decorative

**Other characteristics**

- EU RoHS compliant: Yes

**Packaging information**

- EAN: 8719514269538
- EOC: 871951426953800
- Product title: LED classic 25W ST64 E27 pink D SRT4

**Power**

- Power Factor (Fraction): 0.7

**Power consumption**

- Power factor: 0.5
- Voltage: 220–240 V
- Wattage equivalent: 25 W
- Power: 4.5 W
- Energy consumption kWh/1,000 hours: 5

**Product dimensions and weight**

- Overall height: 140 mm
- Overall length: 140 mm
- Overall width: 64 mm

**Rated values**

- Rated lifetime: 15,000

**Technical specifications**

- Frequency: 50–60
- Diameter: 64 mm
- Dimmable: Only with specific dimmers
- Flickering value (PstLM): 1
- Line Frequency: 50 to 60
- Cap base: E27
- Can it be used in closed luminaires: No

**Packaging dimensions and weight**

- EAN/UPC – product: 8719514269538
- Net weight: 0.04 kg
- Gross weight: 0.07 kg
- Height: 17.7 cm
- Length: 7 cm
- Width: 7.5 cm



Issue date: 2025-12-13  
Version: 0.261

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)