

# PHILIPS

Spot 35W MR16  
GU5.3

LED

4.6W-35W

GU5.3

Warm White

Dimming



8719514307162

A  
↑  
G F



## Bright LED lighting with excellent light quality

Philips LED spots provide a focused bright beam, a long life and significant energy savings

### High-quality light

- No visible flicker
- True incandescent-like warm white light

### Choose a simple replacement for your old lamps

- Similar shape and size as halogen reflectors

# Highlights

## No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimised, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

## True incandescent-like warm white light



This bulb has a colour temperature of 2,700 K, providing you with a warm, tranquil atmosphere, perfect for relaxing. This 2,700 K light is ideal for home lighting design.

## Replaces halogen spots



With its beautifully shaped design and familiar dimensions, this is a modern lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional spot
- Socket: GU5.3
- Lamp Finish: Clear
- Dimmable: Yes
- Bulb material: Glass

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 60 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 360 lm
- Warm-up time to 60% light: 0.5
- Colour Code: 827 | CCT of 2700K
- Luminous efficacy (rated) (nom.): 78 lm/W

## Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Dimmable

## Packaging information

- EAN: 8719514307162
- EOC: 871951430716200
- Product title: LED 35W MR16 WW 60D D RF PF SRT4

## Power consumption

- Power factor: 0.7
- Voltage: 12V AC electronic V
- Wattage equivalent: 35 W
- Energy efficiency label (EEL): F
- Power: 4.6 W
- Energy consumption kWh/1,000 hours: 5

**Product dimensions and weight**

- Overall height: 46 mm
- Overall length: 45.5 mm
- Overall width: 51 mm

**Rated values**

- Rated peak intensity: 480 cd

**Packaging dimensions and weight**

- EAN/UPC - product: 8719514307162
- Net weight: 0.05 kg
- Gross weight: 0.07 kg
- Height: 12.7 cm
- Length: 5.3 cm
- Width: 6.3 cm

**Technical specifications**

- Frequency: -
- EPREL Registration Number: 438110



Issue date: 2026-01-17  
Version: 0.167

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)