

# PHILIPS

Spot

LED


4.9W-/W

GU10

White



8719514308633



## Experience warm white LED light

This Philips LED light bulb provides a beautiful, extra-warm light, an exceptionally long life and immediate, significant energy savings. With its flame colour temperature, this light bulb is the perfect choice for a cosy atmosphere.

### High-quality light

- Cool, energising light

### Choose a simple replacement for your old lamps

- Similar shape and size as halogen reflectors

### Create the right light for your home

- 120° beam – spot

# Highlights

## 3500K [LED Lamps]



This bulb has a colour temperature of 3,500 K providing you with a cool,

energising light, perfect for creating an inviting ambience to host friends or wind down with a book.

## Replaces halogen spots



With its beautifully shaped design and familiar dimensions, this is a modern lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

## 120° beam – spot [LED lamps]

## Replaces halogen spots

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional reflector
- Socket: GU10
- Dimmable: No
- Lamp Finish: Frosted
- Bulb material: Glass

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 3000 K
- Nominal luminous flux: 550 lm
- Warm-up time to 60% light: 0.5
- Colour Code: 830 | CCT of 3000K
- Luminous efficacy (rated) (nom.): 112 lm/W

## Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

## Packaging information

- EAN: 8719514308633
- EOC: 87195143086300
- Product title: LEDClassic 550lm GU10 WH 120D ND1PF SRT4

## Power consumption

- Power factor: 0.5
- Voltage: 220–240 V
- Energy efficiency label (EEL): E
- Power: 4.9
- Energy consumption kWh/1,000 hours: 5

**Product dimensions and weight**

- Overall height: 54 mm
- Overall length: 54 mm
- Overall width: 50 mm

**Technical specifications**

- Frequency: 50-60
- EPREL Registration Number: 1825202

**Packaging dimensions and weight**

- EAN/UPC - product: 8719514308633
- Net weight: 0.05 kg
- Gross weight: 0.07 kg
- Height: 12.7 cm
- Length: 5.3 cm
- Width: 6.3 cm



Issue date: 2025-12-24  
Version: 0.226

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)