

# PHILIPS

Candle 40W B35  
E14 x2

LED

2700K

470 lm

15000 h



8719514310056

A  
↑  
G F



## State-of-the-art LED light bulb for the home

Philips LED frosted candles provide a soft, diffuse light effect and an exceptionally long life. With a pure and elegant design, this light bulb is the perfect match for chandelier fixtures with small (E14) fittings.

### Choose for a sustainable solution

- Long-life bulbs – Last up to 15 years

### Create the right light for your home

- Perfect for decorative fixtures
- A simple LED for everyday use

# Highlights

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs,

and enjoy a perfect lighting solution for over 15 years.

## Perfect for decorative fixtures



Modern lighting in Philips LED candles for use in decorative fixtures, such as in chandeliers, ceiling fans, vanity strips and post lights.

## A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional candle
- Socket: E14
- Dimmable: No

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 470 lm
- Warm-up time to 60% light: 0.5
- Colour Code: 827 | CCT of 2700K
- Luminous efficacy (rated) (nom.): 94 lm/W

## Miscellaneous

- EyeComfort: Yes

## Packaging information

- EAN: 8719514310056
- EOC: 871951431005600
- Product title: LED 40W B35 E14 WW FR ND 2SRT6

## Power consumption

- Power factor: 0.51
- Voltage: 220–240 V
- Wattage equivalent: 40 W
- Energy efficiency label (EEL): F
- Power: 5 W
- Energy consumption kWh/1,000 hours: 5

## Product dimensions and weight

- Overall height: 106 mm
- Overall length: 106 mm
- Overall width: 35 mm

## Technical specifications

- Frequency: 50–60
- EPREL Registration Number: 453225

**Packaging dimensions and weight**

- EAN/UPC - product: 8719514310056
- Net weight: 0.04 kg
- Gross weight: 0.12 kg
- Height: 14.6 cm
- Length: 4.6 cm
- Width: 8.5 cm



Issue date: 2025-12-27  
Version: 0.430

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)