

PHILIPS

Lamp (Dimmable)

LED

7W-26W

E27

Flame

Dimming



8719514313743



State-of-the-art LED for the home

This Philips LED light bulb provides a beautiful, extra-warm light, an exceptionally long life and immediate, significant energy savings. With its flame colour temperature, this light bulb is the perfect choice for a cosy atmosphere.

Dimmable extra warm white light

- Dimmable extra warm white light

Designed to be seen, looks good on and off

- Looks good on and off

Highlights

Dimmable extra warm white light



Offering cosy and warm ambiance in your room with extra warm white lights, which can dim to create your private atmosphere.

Looks good on and off



"These beautiful lamp with visible filament add a sense of style and nostalgia to any room. Looks good on and off."

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Crystal
- Socket: E27
- Lamp Finish: smoky
- Dimmable: Yes
- Bulb material: Glass

Lamp dimensions

- Height: 36.6 cm

Durability

- Number of switch cycles: 20,000
- Ambient temperature range: -20 to +45 °C
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 1800 K
- Nominal luminous flux: 270 lm
- Warm-up time to 60% light: 0.5 s
- Colour Code: 818 | CCT of 1800K
- Correlated Colour Temperature (Nom): 1800
- Luminous Flux: 270 lm
- Stroboscopic effect: 0.4
- Luminous efficacy (rated) (nom.): 38 lm/W

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Efficacy: 38 lm/W
- CE mark: Yes
- EU RoHS compliant: Yes

Packaging information

- EAN: 8719514313743
- EOC: 871951431374300
- Product title: LED giant crystal 26W E27 smoky DIM

Power

- Power Factor (Fraction): 0.7

Power consumption

- Power factor: 0.7
- Voltage: 220–240 V
- Wattage: 7 W
- Wattage equivalent: 26 W
- Power: 7 W
- Energy consumption kWh/1,000 hours: 7

Product dimensions and weight

- Length: 36.6 cm

Rated values

- Rated lifetime: 15,000

Technical specifications

- Frequency: 50–60
- Bulb technology: LED
- Dimmable: Only with specific dimmers
- Flickering value (PstLM): 1
- Line Frequency: 50 to 60
- Cap base: E27
- Can it be used in closed luminaires: No

Packaging dimensions and weight

- EAN/UPC - product: 8719514313743
- Net weight: 0.49 kg
- Gross weight: 0.75 kg
- Height: 42 cm
- Length: 14.5 cm
- Width: 14.5 cm



Issue date: 2026-03-31
Version: 0.258

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com