

# PHILIPS

Candle 48W B35  
E27

LED

2700K

620 lm

15000 h



8719514313910



## Warm white light, no compromise on light quality

Philips LED candles provide a beautiful, warm white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this light bulb is the perfect replacement for your incandescent candles.

### High-quality light

- True incandescent-like warm white light

### Light beyond illumination

- Instant on

### High-quality LED light that lasts for decades

- Designed for the comfort of your eyes

# Highlights

## True incandescent-like warm white light



This bulb has a colour temperature of 2,700 K, providing you with a warm,

tranquil atmosphere, perfect for relaxing. This 2,700 K light is ideal for home lighting design.

## Instant on Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional candle
- Socket: E27
- Lamp Finish: Frosted
- Dimmable: No
- Bulb material: Plastic

## Durability

- Number of switch cycles: 30,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- LED integrated: Yes

## Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 620 lm
- Warm-up time to 60% light: 0.5
- Colour Code: 827 | CCT of 2700K
- Luminous efficacy (rated) (nom.): 95

## Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

## Packaging information

- EAN: 8719514313910
- EOC: 871951431391001
- Product title: LED 48W E27 WW B35NDFR 1SRT4 UK

## Power consumption

- Power factor: 0.51
- Voltage: 220-240 V
- Wattage equivalent: 48
- Energy efficiency label (EEL): F
- Power: 6.5
- Energy consumption kWh/1,000 hours: 7

#### Product dimensions and weight

- Overall height: 104 mm
- Overall length: 104 mm
- Overall width: 35 mm

#### Technical specifications

- Frequency: 50-60
- Bulb technology: LED
- EPREL Registration Number: 406208

#### Packaging dimensions and weight

- EAN/UPC - product: 8719514313910
- Net weight: 0.02 kg
- Gross weight: 0.06 kg
- Height: 14.6 cm
- Length: 3.6 cm
- Width: 6.3 cm



Issue date: 2026-03-21  
Version: 0.381

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)