

PHILIPS

Filament Candle
Clear 40W B35 E14

LED

2200-2700K

470 lm

15000 h

Dimming



8719514324213



Experience dimmable, warm white LED light

Philips LED clear candles provide a beautiful, sparkling light effect and an exceptionally long life. Beautiful both switched on and switched off, this light bulb is the perfect match for chandelier fixtures with small (E14) fittings.

Choose for a sustainable solution

- Saves up to 90% Energy

Create the right light for your home

- Perfect for decorative fixtures

Highlights

Saves up to 90% Energy



Enjoy the energy saving of LEDs without sacrificing light quality. Instantly save over 90% in energy by replacing your existing incandescent or halogen lamps

Perfect for decorative fixtures



Modern lighting in Philips LED candles for use in decorative fixtures, such as in chandeliers, ceiling fans, vanity strips and post lights.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional candle
- Socket: E14
- Lamp Finish: Clear
- Dimmable: Yes
- Bulb material: Glass

Lamp dimensions

- Height: 9.7 cm
- Width: 3.5 cm

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Colour rendering index (CRI): 90
- Colour temperature: 2200-2700 K
- Nominal luminous flux: 470 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 922-927 | CCT of 2200K-2700K

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Dimmable, WarmGlow

Other characteristics

- Efficacy: 138 lm/W

Packaging information

- EAN: 8719514324213
- EOC: 871951432421301
- Product title: LED classic 40W B35 E14 CL WGD90 SRT4 UK

Power consumption

- Power factor: 0.6
- Voltage: 220-240 V
- Wattage: 3.4 W
- Wattage equivalent: 40 W
- Energy efficiency label (EEL): D
- Energy consumption kWh/1,000 hours: 4

Product dimensions and weight

- Length: 9.7 cm

Technical specifications

- Frequency: 50-60 Hz
- EPREL Registration Number: 1109139

Packaging dimensions and weight
[LED classic 40W B35 E14 CL WGD90 SRT4]

- EAN/UPC – product: 8719514324213
- Net weight: 0.01 kg
- Gross weight: 0.03 kg
- Height: 14.6 cm
- Length: 4.6 cm
- Width: 6.3 cm

Packaging dimensions and weight
[LED classic 40W B35 E14 CL WGD90 SRT4 UK]

- EAN/UPC – product: 8719514324213
- Net weight: 0.01 kg
- Gross weight: 0.03 kg
- Height: 14.6 cm
- Length: 4.6 cm
- Width: 6.3 cm



Issue date: 2025-05-24
Version: 0.455

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com