

# PHILIPS

Planet Recessed  
Light 6W

Recessed Lights

2200-2700K

Black

Dimmable



8719514328617



## The more you dim, the warmer the light.

Create the perfect mood with Philips LED WarmGlow Dimmable recessed spots. The more you dim, the warmer the light.

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Colour: Black
- Material: Metal, Plastic

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 25,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: Adjustable – rise and fall
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Beam angle: 36
- Colour consistency: 5 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2200–2700 K
- Luminous efficacy (rated) (nom.): 71

## Miscellaneous

- Especially designed for: Kitchen, Bedroom, Dining Room, Living Room, Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes
- Extra Features: Dimmable

## Other characteristics

- Lamp current: 33 mA

## Product dimensions and weight

- Net weight: 0.195 kg
- Recessed distance: 4 mm
- Overall height: 48 mm
- Overall length: 48 mm
- Overall width: 92 mm
- Recessed ceiling cutout: 6.8–7.8 cm x 6.8–7.8 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Diameter: 92 mm
- Total lumen output fixture: 500
- Bulb technology: LED
- Light colour: 2200–2700
- Mains power: AC 220–240
- Fixture dimmable: Yes
- Wattage bulb included: 6
- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated

## Packaging dimensions and weight

- EAN/UPC – product: 8719514328617
- Net weight: 0.2 kg
- Gross weight: 0.23 kg
- Height: 9.5 cm
- Length: 7 cm
- Width: 11.4 cm



Issue date: 2026-03-21  
Version: 0.337

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)