

# PHILIPS

Magneos Ceiling  
Light 210mm 12W


Ceiling Lights

2700K

Black



8719514328693



## Comfortable LED light that's easy on your eyes

The Philips LED Slim Downlight delivers a natural light effect for use in general lighting applications. It is a slim masterpiece for low ceilings, creating an elegant ambience anywhere at home. Comfortable light that's easy on your eyes.

### Easy to experience

- Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.
- Easy installation

### Premium quality

- EyeComfort – light that's easy on the eyes

### Material and finishing

- High-quality metal material

### Durability

- Long life span up to 25,000 hours

# Highlights


## Suitable for low ceilings Slim design Easy installation

No more hassle with installation. Just fix or hang securely on the wall or ceiling, and plug it in. Your new light fitting is now ready to light up your room!

## EyeComfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, colour rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output and colour for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

## High-quality metal material



Durable and attractive metal material for a strong finish.

## Long life span up to 25,000 hours

Philips LED technology extends your product's lifetime up to 25,000 hours

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Colour: Black
- Material: Metal, Plastic

## Durability

- Number of switch cycles: 12,500
- Nominal lifetime: 25,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Beam angle: 110 degree(s)
- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Luminous efficacy (rated) (nom.): 95 lm/W

## Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Office, Garage
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes

#### Other characteristics

- Lamp current: 110 mA

#### Product dimensions and weight

- Net weight: 0.36 kg
- Overall height: 28 mm
- Overall length: 210 mm
- Overall width: 210 mm

#### Service

- Warranty: 2 year(s)

#### Technical specifications

- Diameter: 210 mm
- Total lumen output fixture: 1150
- Light colour: Warm white light
- Mains power: AC 220-240
- Fixture dimmable: No
- Wattage bulb included: 12
- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated

#### Packaging dimensions and weight

- EAN/UPC – product: 8719514328693
- Net weight: 0.36 kg
- Gross weight: 0.43 kg
- Height: 22 cm
- Length: 3.3 cm
- Width: 21.5 cm



Issue date: 2025-12-06  
Version: 0.481

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)