


SUPERSLIM WiZ CEILING 16W B RD 27-65K TW

Add tunable warm or cool white light to your living spaces with the WiZ Super Slim smart ceiling light. Use with the WiZ app or your voice to dim and brighten or use preset light modes on Wi-Fi set-ups.


PRODUCT HIGHLIGHTS

- Tunable white
- Dimensions: Ø292
- IP20/Plastic/White




Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Monitor your energy consumption

Get an overview of the energy consumption of your lights with the WiZ app. Easily access a weekly or daily report to help you stay on top of your energy consumption at home.



Create your perfect light scene

Make your own mix of different colour and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energising cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



Dim your smart lights even without a dimmer

Simply adjust lights to your desired brightness level using your smartphone, the WiZ control accessory or just your voice. No need to install an expensive dimmer!



Control smart lighting the way you like it

WiZ enables you to control smart lighting in multiple ways. Adjust lights with your smartphone, voice, the WiZ remote control or by using the existing wall switch to toggle between two favourite modes. Works with Google Home, Alexa and Siri Shortcuts.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Lamp shape: Round

DESIGN AND FINISHING

Colour: Black
Material: Metal Plastic

DURABILITY

Average life (at 2.7 hrs/day): 20 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 20,000

EXTRA FEATURE/ACCESSORY INCL.

Adjustable spot head: No
Dimmable with remote control: Yes
LED integrated: Yes
Remote control included: No

LIGHT CHARACTERISTICS

Colour consistency: 6 SDCM
Colour rendering index (CRI): 80
Warm-up time to 60% light: <2

MISCELLANEOUS

Especially designed for: Functional

OTHER CHARACTERISTICS

Lamp current: 130 mA
Efficacy: 93 lm/W

POWER CONSUMPTION

Power factor: 0.5
Voltage: 220-240 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.58 kg
Height: 2.3 cm
Length: 29.2 cm
Width: 29.2 cm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Lifetime up to: 20,000 h
Diameter: 292 mm
Total lumen output fixture: 1500
Light colour: 2700-6500
Fixture dimmable: Wireless Dim – Do not use with a dimmer
LED: Yes
Built-in LED: Yes
Wattage bulb included: 16
IP code: IP20
Class of protection: Class II

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8719514338036
Net weight: 0.59 kg
Gross weight: 0.69 kg
Height: 30 cm
Length: 2.8 cm
Width: 29.5 cm
Material number (12NC): 929002685201



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.