

PHILIPS

Bulb

Ultra Efficient

4 W-60 W

E27

Cool White

Light that's **easy** on your eyes 



*Designed for the comfort of your eyes.
See below for more information.

8719514343801



Clear LED candle bulbs add a sparkle to your home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

Choose for a sustainable solution

- Saves up to 90% Energy
- Long life bulb - Lasts up to 50 years

Designed to be seen, looks good on and off

- Classic glass LED

Highlights

Saves up to 90% Energy



Enjoy the energy saving of LEDs without sacrificing light quality. Instantly save over 90% in energy by

replacing your existing incandescent or halogen lamps

Long life bulb - Lasts up to 50 years



With a lifetime of up to 50,000 hours, you can reduce the hassle of frequently replacing your light bulbs and enjoy a perfect lighting solution for over 50 years.

Glass Clear Design

The look you love, the performance you expect. Classic clear glass designs that replicate the beautiful sparkling light of traditional bulbs, for a perfect fit throughout your home.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: E27
- Dimmable: No

Durability

- Number of switch cycles: 500,000
- Nominal lifetime: 50,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Nominal luminous flux: 840 lm
- Warm-up time to 60% light: 0.5
- Colour Code: 840 | CCT of 4000K
- Luminous efficacy (rated) (nom.): 210 lm/W

Miscellaneous

- EyeComfort: Yes
- LED innovations: UltraEfficient

Packaging information

- EAN: 8719514343801
- EOC: 871951434380100
- Product title: LED CLA 60W A60 E27 4000K CL EELA SRT4

Power consumption

- Power factor: 0.4
- Voltage: 220-240 V
- Wattage equivalent: 60 W
- Energy efficiency label (EEL): A
- Power: 4 W
- Energy consumption kWh/1,000 hours: 4

Product dimensions and weight

- Overall height: 105 mm
- Overall length: 105 mm
- Overall width: 60 mm

Technical specifications

- Frequency: 50-60
- EPREL Registration Number: 1370030

Packaging dimensions and weight

- EAN/UPC - product: 8719514343801
- Net weight: 0.03 kg
- Gross weight: 0.05 kg
- Height: 14.6 cm
- Length: 6.5 cm
- Width: 6.3 cm



Issue date: 2025-12-27
Version: 0.195

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com