

# PHILIPS

Filament Bulb amber  
7W (Eq.50W) A60 E27

Smart LED

Tunable white

Glass

Easy plug and play

Control with the WiZ app or  
your voice

8719514372023



## Choose from warm or cool white light

Get smart light with a vintage look with the Philips Smart LED Filament bulb with an E27 base, which offers an amber coating with warm or cool white light. This bulb is WiZ-connected. Use with your existing Wi-Fi to control with the WiZ app or your voice.

### Smart control

- Connected by WiZ

### Smart features

- SpaceSense motion detection
- Smart automations

### Light modes

- Tunable white light
- Low dimming
- Decorative bulb

# Highlights

## Connected by WiZ

Fully compatible with all Connected by WiZ products – use the WiZ app to set up and unlock all the benefits of smart lighting.

## SpaceSense motion detection



Turn your lights into motion sensors using integrated SpaceSense technology, so they switch on automatically when you enter the room – all you need are two or more Connected by WiZ lights or devices.

## Smart automations

Schedule your lights to work in sync with your routine, switching on automatically when you wake up, or switching off when nobody's at home to save energy.

## Tunable white light

Easily adjust from cool, bluish hues that enhance visibility and focus to soft, warmer tones for relaxing in the evening (CCT range 2,200 K–6,500 K).

## Low dimming

Dim your light smoothly from full brightness down to 1% to achieve the right level of light for whatever you're doing.

## Decorative bulb

The visible filament creates a warm, decorative focal point that enhances a room's atmosphere even when the light is switched off.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: A60
- Socket: E27
- Type of glass: Amber
- Lamp Finish: Amber
- Dimmable: Yes

## Lamp dimensions

- Weight: 0.042 kg

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 20,000
- Nominal lifetime: 15,000

## Extra feature/accessory incl.

- LED integrated: Yes
- Solar Energy: No
- Warm glow dimmable light: No

## Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 90
- Colour temperature: 2000–5000 K
- Light Colour Category: Tunable white
- Nominal luminous flux: 640 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Luminous efficacy (rated) (nom.): 91

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 43 mA

## Packaging information

- EAN: 8719514372023
- EOC: 871951437202300
- Product title: PHI WFB 50W A60 E27 920–50 Amb 1PF/6

**Power consumption**

- Power factor: 0.5
- Voltage: AC 220-240 V
- Wattage equivalent: 50 W
- Energy efficiency label (EEL): F
- Power: 7 W
- Energy consumption kWh/1,000 hours: 7

**Product dimensions and weight**

- Overall height: 10.6 mm
- Overall length: 10.6 mm
- Overall width: 6 mm

**Rated values**

- Rated lifetime: 15,000
- Rated luminous flux: 640 lm
- Rated power: 7 W

**Service**

- Warranty: 2 year(s)

**Technical specifications**

- Frequency: 50-60
- Bulb technology: LED
- EPREL Registration Number: 1901124
- Flux measurement reference: Sphere

**The bulb**

- Software upgradable: Yes

**What's supported**

- Compatible with Effects feature: Yes
- WiFi: 802.11b/g/n
- Defined support period: Minimum of 60 months after introduction date
- Max. number of accessories: 9999
- Compatible operating systems: iOS, Android
- Communication protocol: Bluetooth, WiFi (2.4GHz)
- Compatibility with third-party systems: Alexa, Google Home, Homey, IFTTT, Matter, Samsung SmartThings, Siri Shortcuts
- Matter functionality: Via third-party hubs (Wi-Fi)

**Packaging dimensions and weight**

- EAN/UPC - product: 8719514372023
- Net weight: 0.04 kg
- Gross weight: 0.09 kg
- Height: 16 cm
- Length: 7 cm
- Width: 7 cm



Issue date: 2026-06-13  
Version: 0.333

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)