

PHILIPS

Candle 4.9W
(Eq.40W) C37 E14 x2

Smart LED

Full colour

Plastic

Easy plug and play

Control with the WiZ app or
your voice



8719514372726



Colourful light that matches your mood

Add smart light to your candelabra fittings with a Philips Smart LED full-colour candle bulb with an E14 base. This bulb is WiZ-connected. Use with your existing Wi-Fi to control with the WiZ app or your voice.

Smart control

- Connected by WiZ

Smart features

- SpaceSense motion detection

Smart devices

- Matter-certified

Highlights

Connected by WiZ

Fully compatible with all Connected by WiZ products – use the WiZ app to set up and unlock all the benefits of smart lighting.

SpaceSense motion detection



Turn your lights into motion sensors using integrated SpaceSense technology, so they switch on automatically when you enter the room – all you need are two or more Connected by WiZ lights or devices.

Matter-certified



Control it your way using your preferred smart home assistant – Matter-compatible for seamless integration with Alexa, Google Home and Apple Home.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: C37
- Socket: E14
- Type of glass: Frosted
- Lamp Finish: Frosted
- Dimmable: Yes

Lamp dimensions

- Weight: 0.045 kg

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

Extra feature/accessory incl.

- LED integrated: Yes
- Solar Energy: No
- Warm glow dimmable light: No

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 90
- Colour temperature: 2200-6500 K
- Light Colour Category: Full colour
- Nominal luminous flux: 470 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Luminous efficacy (rated) (nom.): 95

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 40 mA

Packaging information

- EAN: 8719514372726
- EOC: 871951437272600
- Product title: PHI WFB 40W C37 E14 922-65 RGB 2PF/6

Power consumption

- Power factor: 0.48
- Voltage: AC 220-240 V
- Wattage equivalent: 40 W
- Energy efficiency label (EEL): F
- Power: 4.9 W
- Energy consumption kWh/1,000 hours: 5

Product dimensions and weight

- Overall height: 11.6 mm
- Overall length: 11.6 mm
- Overall width: 3.9 mm

Rated values

- Rated lifetime: 15,000
- Rated luminous flux: 470 lm
- Rated power: 4.9 W

Service

- Warranty: 2 year(s)

Technical specifications

- Frequency: 50-60
- Bulb technology: LED
- EPREL Registration Number: 1877837
- Flux measurement reference: Sphere

The bulb

- Software upgradable: Yes

What's supported

- Compatible with Effects feature: Yes
- WiFi: 802.11b/g/n
- Defined support period: Minimum of 60 months after introduction date
- Max. number of accessories: 9999
- Compatible operating systems: iOS, Android
- Communication protocol: Bluetooth, WiFi (2.4GHz)
- Compatibility with third-party systems: Alexa, Google Home, Homey, IFTTT, Matter, Samsung SmartThings, Siri Shortcuts
- Matter functionality: Via third-party hubs (Wi-Fi)

Packaging dimensions and weight

- EAN/UPC - product: 8719514372726
- Net weight: 0.09 kg
- Gross weight: 0.15 kg
- Height: 16 cm
- Length: 7 cm
- Width: 10.5 cm



Issue date: 2026-06-06
Version: 0.283

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com