

# PHILIPS

Skies Wall Light 14W  
E27 P45 No-bulb

Outdoor luminaires

Skies

grey



8719514385344



## Saving in style

This elegant light grey Philips ceiling light invites you to settle with a good book in the shine of the light. It casts warm white energy-saving light and it makes your garden or terrace immediately look more appealing.

### Bring design into your garden

- Choose contemporary style
- Choose outdoor ceiling lights
- High-quality aluminium and superior synthetics

### Special characteristics

- Suitable for wall and ceiling installation
- Easy to set up for every application

### Designed for your garden

- IP44 - weatherproof

# Highlights

## Choose contemporary style

Designed in Europe, this lamp has a unique design signature to help you create a contemporary outdoor look.


## Choose ceiling lights

Make the most of your outdoor space with this ceiling light, perfect for lighting your house porch or patio.

## High quality material

This Philips lamp is made specifically for outdoor spaces. It's hard-wearing and built to last, so it will light up your garden night after night. It's constructed from high-quality die-cast aluminium and superior synthetics.

## Wall and ceiling installation



Install this lamp as a wall light or ceiling light, just the way you like it.

## Easy to set up

This lamp and the fittings are designed for a straightforward installation with all the useful things that you need to get up and running included in the box, like a Torx key and Torx screw. You'll find clear guidance about where you can install the product and relevant information about water-resistant IP ratings.

## IP44 - weatherproof



This Philips outdoor light is especially designed for humid outdoor environments. It was tested rigorously to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This outdoor light is designed with IP44: it is protected against splashing water. This product is most commonly used and ideal for general outdoor use.

# Specifications

## Design and finishing

- Colour: Grey
- Material: Metal

## Durability

- Nominal lifetime: 10,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Fully weatherproof: Yes
- LED integrated: No

**Garden area**

- Garden area: Garden and Patio

**Miscellaneous**

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- Extra Features: Water Resistant

**Product dimensions and weight**

- Net weight: 1.000 kg
- Overall height: 81 mm
- Overall length: 260 mm
- Overall width: 260 mm

**Service**

- Warranty: 2 year(s)

**Technical specifications**

- Bulb technology: LED
- Mains power: 50-60 Hz
- Energy class included light source: bulb not included
- Fitting/cap: E27
- Wattage bulb included: -
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class II – Double Insulated
- Number of light sources: 2

**Packaging dimensions and weight**

- EAN/UPC - product: 8719514385344
- Net weight: 1.07 kg
- Gross weight: 1.24 kg
- Height: 279 mm
- Length: 95 mm
- Width: 274 mm



Issue date: 2026-03-31  
Version: 0.360

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)