

PHILIPS

Superslim Ceiling Light 15W

Outdoor luminaires

4000K

Black

SceneSwitch; Water Resistant



8719514418011



One fixture. Your switch. Three light settings.

Create the right mood by changing brightness. Philips' SceneSwitch LED ceiling light lets you enjoy three brightness settings that are perfect for every moment. No dimmer or additional installation is required – all you need is your existing switch.

Light effect

- Provides a bright white light

Sustainable light solutions

- Energy saving
- Philips offers a 5-year warranty on the LED module and driver

Bring design into your garden

- Choose outdoor ceiling lights

Designed for your garden

- IP54 - weather-proof (outdoor lighting)

Designed for your living room and bedroom

- High-quality materials

Highlights

Superior light quality Energy saving



This Philips energy-saving lamp conserves energy compared with traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

5-year warranty on LED system



On top of the standard 2-year warranty for this lamp, Philips offers a 5-year warranty on the LED system, meaning the LED module and the driver in this lamp.

Choose ceiling lights

Make the most of your outdoor space with this ceiling light, perfect for lighting your house porch or patio.

IP54 - weather-proof (outdoor lighting)

This Philips outdoor light is especially designed for humid outdoor environments. It was tested rigorously to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This outdoor light is designed with IP54: it is protected against splashing water. This product is most commonly used and ideal for general outdoor use.

High-quality materials

This lamp is sculpted from layered patterns of high-quality materials with superior finishing. This ensures a solid and long lasting product that will enhance your home for many years to come.

Specifications

Bulb characteristics

- Dimmable: Yes

Design and finishing

- Colour: Black
- Material: Metal, Plastic

Durability

- Nominal lifetime: 20,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Anti-rust anti-dust: Yes
- click!FIX mounting: Yes
- compatible with all dimmers: No
- Day-and-night sensor: No
- Defined light beams: Yes
- Dimmable: No
- Dimmable with remote control: No
- FFP - Frustration-Free Pack: No
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion and day-and-night sensor: No
- Motion sensor: No
- Portable: No
- Remote control included: No
- Rotates freely in any direction: No
- Solar Energy: No
- Tilttable head (up-down): No
- USB charging: No
- Centrepiece: Yes
- Plug type: No plug

Garden area

- Garden area: Garden and Patio

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 4000 K

Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- Extra Features: SceneSwitch, Water Resistant

Power consumption

- Power: 15

Product dimensions and weight

- Net weight: 0.47 kg
- Overall height: 23 mm
- Overall length: 250 mm
- Overall width: 250 mm

Service

- Warranty: 5 year(s)

Technical specifications

- Total lumen output fixture: 1500
- Bulb technology: LED
- Light colour: Cool white light
- Energy class included light source: E
- IP code: IP54 | Dust-accumulation-protected and splash-proof
- Class of protection: Class II – Double Insulated
- Light source replaceable: No

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8719514418011
- Net weight: 0.47 kg
- Gross weight: 0.54 kg
- Height: 25 cm
- Length: 2.8 cm
- Width: 24.5 cm



Issue date: 2026-04-15
Version: 0.279

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com