

Ivory Desk Light

Desk Lights

2700/3600/5000 K

White

Dimmable

8719514420410



Comfortable LED light that's easy on your eyes

With its robust design and optimal performance, the Philips LED Performance desk light is the perfect luminaire that brings quality and brightness to any home spaces. Comfortable light that's easy on your eyes.

Premium quality

- EyeComfort – light that's easy on the eyes

Control

- Step dimming

Highlights

EyeComfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, colour

rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output and

colour for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Step dimming

Select from different dimming levels to create the right mood for the moment.

Specifications

Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

Design and finishing

- Colour: White
- Material: Metal, Plastic

Durability

- Number of switch cycles: 15,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 90
- Colour temperature: 2700-4000-6500 K
- Luminous efficacy (rated) (nom.): 26

Miscellaneous

- Especially designed for: Bedroom, Living Room, Office
- Style: Contemporary
- Type: Desk Lights
- EyeComfort: Yes
- Extra Features: Dimmable

Other characteristics

- Lamp current: 1000 mA

Product dimensions and weight

- Net weight: 0.5 kg
- Overall height: 353 mm
- Overall length: 340 mm
- Overall width: 114 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Total lumen output fixture: 130
- Light colour: Tunable white light
- Mains power: 5 V
- Wattage bulb included: 5
- IP code: IP20 | Finger-protected
- Class of protection: Class III – Safe Extra Low Voltage

Packaging dimensions and weight

- EAN/UPC - product: 8719514420410
- Net weight: 0.5 kg
- Gross weight: 0.75 kg
- Height: 41.1 cm
- Length: 12.5 cm
- Width: 17.6 cm



Issue date: 2026-02-17
Version: 0.347

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com