

# PHILIPS

## Einstein Desk Light

### Desk Lights

2800/4000/5100K

Dark grey

Dimmable



8719514431195



## Comfortable LED light that's easy on your eyes

With its robust design and optimal performance, the Philips LED Performance desk light is the perfect luminaire that brings quality and brightness to any home spaces. Comfortable light that's easy on your eyes.

### Light effect

- SceneSwitch colour change

### Premium quality

- EyeComfort – light that's easy on the eyes

### Control

- Step dimming

# Highlights

## SceneSwitch colour change

SceneSwitch Colour Change lets you set the overall mood of a living space at home. Stay focused with cool daylight, be more productive with cool white light or wind down and relax with warm white light. In essence, consumers can control the lights in their home according to their daily activities.

## EyeComfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, colour rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable

light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output and colour for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

## Step dimming

Select from different dimming levels to create the right mood for the moment.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

## Design and finishing

- Colour: Dark Grey
- Material: Metal, Plastic

## Durability

- Number of switch cycles: 15,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 94
- Colour temperature: 2700-4000-6500 K
- Luminous efficacy (rated) (nom.): 42 lm/W

## Miscellaneous

- Especially designed for: Bedroom, Living Room, Office
- Style: Contemporary
- Type: Desk Lights
- EyeComfort: Yes
- Extra Features: Dimmable

## Other characteristics

- Lamp current: 180 mA

## Product dimensions and weight

- Net weight: 3.44 kg
- Overall height: 457 mm
- Overall length: 200 mm
- Overall width: 268 mm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Total lumen output fixture: 630
- Light colour: 2800/4000/5100
- Mains power: AC 220-240
- Wattage bulb included: 15
- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated

## Packaging dimensions and weight

- EAN/UPC – product: 8719514431195
- Net weight: 2.3 kg
- Gross weight: 3.45 kg
- Height: 51 cm
- Length: 23.2 cm
- Width: 26.6 cm



Issue date: 2025-08-30  
Version: 0.324

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)