

# PHILIPS

Moire Ceiling Light  
36 W

Ceiling Lights

2700K

White



8719514431706



## Comfortable LED light that's easy on your eyes

Philips LED luminaires provide light that is designed for the comfort of your eyes.

### Light effect

- This ceiling light features Interlaced Optics technology, cleverly redistributing the light to enhance your overall lighting experience. This fixture's lens has a pyramid micro-structure that diffuses and evenly distributes the light, making it easier on the eyes.

### Easy to experience

- Easy installation

### Light effect

- Uniform light distribution

### Premium quality

- Easy to clean

### Durability

- Long life span up to 15,000 hours

# Highlights

## Interlaced Optics

This ceiling light features Interlaced Optics technology, cleverly redistributing the light to enhance your overall lighting experience. This fixture's lens has a pyramid micro-structure that diffuses and evenly distributes the light, making it easier on the eyes.

## Easy installation

No more hassle with installation. Just fix or hang securely on the wall or ceiling, and plug it in. Your new light fitting is now ready to light up your room!

## Uniform light distribution

Throw light across your rooms in an even and uniform manner.

## Easy to clean

Smooth and easy-to-clean materials mean your home always looks attractive from floor to ceiling.

## Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Colour: White
- Material: Metal, Plastic

## Durability

- Number of switch cycles: 15,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Warm-up time to 60% light: 2
- Luminous efficacy (rated) (nom.): 100

## Miscellaneous

- Especially designed for: Kitchen, Bedroom, Dining Room, Garage, Living Room, Office
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes

## Other characteristics

- Lamp current: 180 mA

## Product dimensions and weight

- Net weight: 1.1 kg
- Overall height: 80 mm
- Overall length: 490 mm
- Overall width: 490 mm

## Service

- Warranty: 5 year(s)

## Technical specifications

- Diameter: 490 mm
- Total lumen output fixture: 3600
- Bulb technology: LED
- Light colour: Warm white light
- Mains power: AC 220-240
- Fixture dimmable: No
- IP code: IP20
- Class of protection: Class I – Earthed

## The bulb

- Software upgradable: No

### What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

### Packaging dimensions and weight

- EAN/UPC - product: 8719514431706
- Net weight: 1.05 kg
- Gross weight: 2.18 kg
- Height: 52.2 cm
- Length: 9.7 cm
- Width: 52.2 cm



Issue date: 2026-05-13  
Version: 0.277

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)