

PHILIPS

Mauve Ceiling Light
16 W

Ceiling Lights

2700K

White

Sensor



8719514431843



Motion sensing light for convenience and extra energy saving

Increase convenience while saving energy. Philips' motion-sensing LED ceiling light is easily turned on and off by a sensor, which means you can leave or enter rooms without fumbling for a switch. Its wide detection range and instant-on LED technology means that your home's lighting is only on when you need it

Easy to experience

- With its built-in automatic motion sensor, this luminaire switches on automatically when people walk by.
- Easy installation

Durability

- Energy saving

Highlights

Integrated motion sensor

Easy installation

No more hassle with installation. Just fix or hang securely on the wall or

ceiling, and plug it in. Your new light fitting is now ready to light up your room!

Energy saving

Saves energy – which is good for your bills, and the environment.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Colour: White
- Material: Metal, Plastic

Durability

- Number of switch cycles: 15,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Warm-up time to 60% light: 2
- Luminous efficacy (rated) (nom.): 106 lm/W

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Office, Garage
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- Extra Features: Sensor

Other characteristics

- Lamp current: 140 mA

Product dimensions and weight

- Net weight: 0.5 kg
- Overall height: 72 mm
- Overall length: 320 mm
- Overall width: 320 mm

Service

- Warranty: 5 year(s)

Technical specifications

- Diameter: 320 mm
- Total lumen output fixture: 1700
- Light colour: 2700
- Mains power: AC 220-240
- Fixture dimmable: No
- IP code: IP20 | Finger-protected
- Class of protection: Class I – Earthed

Packaging dimensions and weight

- EAN/UPC – product: 8719514431843
- Net weight: 0.48 kg
- Gross weight: 0.79 kg
- Height: 34.2 cm
- Length: 8.2 cm
- Width: 34.2 cm



Issue date: 2025-08-30
Version: 0.272

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com