

# PHILIPS

Ozziet Ceiling Light  
36 W

Ceiling Lights

4000K

White

Dimmable



8719514432109



## One fixture. Two light zones. Three settings.

This modern sleek slim white design looks as good off as it does on. The clean round lines of the main light are accented with a clever linear edge light. Combine the two lights together and create three unique light settings. The main downlight has a cool 4,000 k output and the linear edge accent light provides warm 2,700 k output. The lamp is available in three sizes, and therefore fits perfectly in any room of your house. The handy memory feature helps you recall your latest setting. So, if pure white design with many features is your thing, the Ozziet is the perfect ceiling light for you.

### Designed for your living room and bedroom

- Perfect to relax and socialise

### Match your interior

- Super slim design

### Easy to experience

- Memorise your favourite mode for easy selection
- Easy installation

### Light effect

- Dual zone light

# Highlights

## Perfect to relax and socialise

The living room is the heart of any home: a place where families gather to relax and guests socialise. Lighting for your living room and bedroom has to be flexible and easy to adjust to its different uses throughout the day. Careful placement of different light sources and playing with light layering helps create the feeling of space and gives the room a warm and welcoming feel.

## Super slim design

Slim design is ideal for low-ceiling rooms, sitting flush against the surface.

## Memorise your favourite mode for easy selection

Whether you prefer a warm glow for cosy evenings or a bright white light for focus, the system memorises your favourites for easy selection.

## Easy installation

No more hassle with installation. Just fix or hang securely on the wall or ceiling, and plug it in. Your new light fitting is now ready to light up your room!

## Dual zone light

Changing the ambiance in your room has never been easier. Philips' SceneSwitch Dual zone LED ceiling light lets you set the mood with three unique settings. The combination of main and linear edge light give you options that are perfect for your get together, concentrating and cosy moments. No dimmer or installation required – all you need is your existing switch.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

## Design and finishing

- Colour: White
- Material: Plastic

## Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 20,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Warm-up time to 60% light: 2
- Luminous efficacy (rated) (nom.): 113

## Miscellaneous

- Especially designed for: Kitchen, Bedroom, Dining Room, Garage, Living Room, Office
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- Extra Features: Dimmable

## Other characteristics

- Lamp current: 180 mA

## Product dimensions and weight

- Net weight: 1.55 kg
- Overall height: 55 mm
- Overall length: 500 mm
- Overall width: 500 mm

## Service

- Warranty: 5 year(s)

### Technical specifications

- Diameter: 500 mm
- Total lumen output fixture: 4100
- Bulb technology: LED
- Light colour: Cool white light
- Mains power: AC 220-240
- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated

### Packaging dimensions and weight

- EAN/UPC – product: 8719514432109
- Net weight: 1.55 kg
- Gross weight: 2.15 kg
- Height: 52.8 cm
- Length: 5.9 cm
- Width: 52.5 cm

### The bulb

- Software upgradable: No

### What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable



Issue date: 2026-04-15  
Version: 0.271

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)