

# PHILIPS

## Star Ceiling/Wall Spotlight 18W

Ceiling/Wall Spotlights


2700K

Black

Dimmable; ClickFix



8719514435438



## Accent your home with light

This Philips myLiving Star LED spot speaks of timeless elegance with its chrome leg and powdered black paint body. With this Philips LED dimmable spot, you can smoothly dim to the right light level – from bright functional for everyday tasks, to a soft light for relaxed time.

### Sustainable light solutions

- Compatible with in-wall dimmers
- High quality LED light

### Advanced LED light

- Warm white light

### Special characteristics


- Adjustable spot head

### Lighting for your convenience and peace of mind

- Lamp lifetime for up to 30 years of use
- 5-year warranty for peace of mind

# Highlights

## Compatible with in-wall dimmers



Adjust the brightness of this Philips light with an in-wall dimmer (not included) to set the mood in the room, highlight a feature of your home and more.

## High quality LED light



The LED technology integrated into this Philips lamp is a unique solution developed by Philips. It turns on instantly, enables an optimal light output and brings out vivid colours in your home.

## Warm white light



This light uses the very latest lighting technology by Philips with the new warm white state-of-the-art high power LEDs providing a glow of light with a colour temperature of 2700 Kelvin.

## Adjustable spot head



Direct the light where you want it most by simply adjusting, rotating or tilting the spot head of the lamp.

## Lifetime for up to 30 years

LED lights last longer, avoiding the hassle of frequent light source replacement. This significantly reduces waste, but also saves you money in the long term.

## 5-year warranty

All our spot lights are built to last. They come with a full 5-year warranty on the complete product, ensuring you will enjoy long-lasting quality lighting every day.

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Colour: Black
- Material: Metal

## Durability

- Number of switch cycles: 30,000
- Nominal lifetime: 30,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

**Extra feature/accessory incl.**

- Anti-rust anti-dust: No
- Bi-directional light beams: No
- click!FIX mounting: Yes
- Day-and-night sensor: No
- Defined light beams: No
- Dimmable: No
- Dimmable with remote control: No
- FFP - Frustration-Free Pack: No
- Fully weatherproof: No
- LED integrated: Yes
- Motion and day-and-night sensor: No
- Motion sensor: No
- Perfectly suited for creating ambience: Yes
- Perfectly suited for orientation lighting: Yes
- Portable: No
- Protection sleeve included: No
- Remote control included: No
- Resistant high-quality material: Yes
- Rotates freely in any direction: Yes
- Solar Energy: No
- Tilttable head (up-down): Manual
- USB charging: No
- Centrepiece: No
- Centrepiece: No
- Plug type: No plug

**Light characteristics**

- Beam angle: 45 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Luminous efficacy (rated) (nom.): 110 lm/W

**Miscellaneous**

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Office, Hall
- Style: Contemporary
- Type: Ceiling/Wall Spotlights
- EyeComfort: Yes
- Extra Features: Dimmable, ClickFix

**Product dimensions and weight**

- Net weight: 1.09 kg
- Cable length: 1,120
- Overall height: 82 mm
- Overall length: 560 mm
- Overall width: 60 mm

**Service**

- Warranty: 5 year(s)

**Technical specifications**

- Total lumen output fixture: 2000
- Light colour: Warm white light
- Mains power: AC 220-240
- Fixture dimmable: Yes
- Energy class included light source: F
- Wattage bulb included: 18
- IP code: IP20 | Finger-protected
- Class of protection: Class I – Earthed
- Light source replaceable: Yes
- Number of light sources: 4

**Packaging dimensions and weight**

- EAN/UPC – product: 8719514435438
- Net weight: 1.09 kg
- Gross weight: 1.38 kg
- Height: 57.7 cm
- Length: 7.2 cm
- Width: 9.2 cm



Issue date: 2025-12-06  
Version: 0.272

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)