

# PHILIPS

Filament Candle  
Clear 25W S26 E14

LED

2.5 W-25 W

E14



8719514441439



## A light bulb like no other

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your clear incandescent bulbs.

### High-quality light

- Designed for the comfort of your eyes

### Create the right light for your home

- A simple LED for everyday use

# Highlights

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: S26
- Socket: E14
- Lamp Finish: Clear
- Dimmable: No
- Bulb material: Glass

## Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- LED integrated: Yes

## Light characteristics

- Beam angle: 270
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 250 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 827 | CCT of 2700K
- Luminous efficacy (rated) (nom.): 100

## Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

## Packaging information

- EAN: 8719514441439
- EOC: 871951444143900
- Product title: LED classic 25W T25S E14 CL ND SRT6

## Power consumption

- Power factor: 0.4
- Voltage: 230 V
- Wattage equivalent: 25
- Energy efficiency label (EEL): F
- Power: 2.5
- Energy consumption kWh/1,000 hours: 3

## Product dimensions and weight

- Overall height: 61 mm
- Overall length: 61 mm
- Overall width: 26 mm

## Technical specifications

- Frequency: 50
- Bulb technology: LED
- EPREL Registration Number: 1031264

## Packaging dimensions and weight

- EAN/UPC - product: 8719514441439
- Net weight: 0.01 kg
- Gross weight: 0.02 kg
- Height: 14.7 cm
- Length: 3 cm
- Width: 7.5 cm



Issue date: 2026-03-21  
Version: 0.267

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)