

# PHILIPS

## Tyla Wall Light 9W

Outdoor luminaires

4000K

Antracite

Sensor; Water Resistant



8719514476875



## Enjoy beautiful garden light whether walking or relaxing

The Philips Tyla LED outdoor wall light in anthracite grey frames cosy light within a durable die-cast aluminium surround. It creates appealing ambience with cool white light when idle and automatically brightens when people are present.

### Sustainable light solutions

- Long lifetime up to 25,000 hours

### Advanced LED light

- 5-year warranty on LED system
- High-quality LED light

### Premium quality

- High-quality aluminium and superior synthetics

### Designed for outdoors

- IP44 – weatherproof

### Special characteristics

- Dual-brightness light
- Motion and dusk-to-dawn sensor integrated

8719514476875

**High-quality light**

- Warm white light 2,700 K

# Highlights

## Long lifetime up to 25,000 hours



Reliable high-quality LED light lasts up to 25,000 hours. You can rest easy knowing that you won't have to worry about maintenance for years, while enjoying the perfect garden light every night.

## 5-year warranty on LED system



In addition to the standard 2-year warranty offered for this luminaire, Philips also offers a 5-year warranty on the LED system (the LED module and driver).

## High-quality LED light



These LED lights use a unique technology developed by Philips. They turn on instantly and produce optimal light output that brings out the vivid colours in your garden.

## High-quality aluminium and superior synthetics



This Philips light is made specifically for outdoor spaces. It's hard-wearing and built to last, so it will light up your garden night after night. It's constructed from high quality die-cast aluminium and superior synthetics.

## IP44 – weatherproof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water – perfect for general outdoor use.

## Dual-brightness light

Create a flexible and appealing ambience with the dual-brightness feature. The light dims when idle and automatically brightens when people are present, delivering the right level of light whenever you need it.

## Motion and dusk-to-dawn sensor integrated



With a built-in motion sensor, these lights automatically welcome you when you return home after dark, or light up when visitors arrive. The unique dusk-to-dawn feature turns the lights on automatically when it gets dark outside – perfect for those long summer evenings or to ensure your safety.

## Warm white light 2,700 K



Did you know that different shades of white light are identified by different colour temperatures, measured in Kelvin (K)? Lower colour temperatures produce a warm, cosy white light, while higher colour temperatures produce a cool, more energising white light. This luminaire produces warm, relaxing light at 2,700 K.

# Specifications

## Design and finishing

- Colour: Anthracite
- Material: Aluminium

## Durability

- Nominal lifetime: 25,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- 5 year warranty on the LED module: Yes
- Anti-rust anti-dust: Yes
- Day-and-night sensor: Yes
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion sensor: Yes
- Solar Energy: No
- Warm White Light: No
- Centrepiece: No

## Garden area

- Garden area: Garden and Patio

## Light characteristics

- Colour rendering index (CRI): 80

## Miscellaneous

- Especially designed for: Garden and Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- Extra Features: Sensor, Water Resistant

## Product dimensions and weight

- Net weight: 0.682 kg
- Height: 18.8 cm
- Length: 18.4 cm
- Width: 15.8 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Total lumen output fixture: 930
- Light colour: 4000
- Mains power: 220-240
- Energy class included light source: F
- IP code: IP44
- Class of protection: Class I
- Light source replaceable: No

## Packaging dimensions and weight

- EAN/UPC – product: 8719514476875
- Net weight: 0.68 kg
- Gross weight: 1.03 kg
- Height: 20 cm
- Length: 17.5 cm
- Width: 21.5 cm



Issue date: 2025-06-12  
Version: 0.351

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)