



IMAGEO 3x adjustable spotlight

With three adjustable spots, the WiZ Imageo smart build-on spotlight in white offers warm or cool white light for any room. Use with your existing Wi-Fi to control with the WiZ app or your voice.

PRODUCT HIGHLIGHTS

- Tunable white
- Plate Dimensions: 8*44 cm
- IP20/Metal/White



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Control with any Matter smart home platform

This product is Matter-certified, allowing easy control through Google Home, Amazon Alexa, Apple Home or any other Matter-based smart home platform of your choice.



Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and get the lights to turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.




Monitor your energy consumption

Get an overview of the energy consumption of your lights with the WiZ app. Easily access a weekly or daily report to help you stay on top of your energy consumption at home.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energising cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



Control smart lighting the way you like it

WiZ enables you to control smart lighting in multiple ways. Adjust lights with your smartphone, voice, the WiZ remote control or by using the existing wall switch to toggle between two favourite modes. Works with Google Home, Alexa and Siri Shortcuts.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Lamp shape: Rectangle
Dimmable: Yes

DESIGN AND FINISHING

Colour: White
Material: Metal

DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 15,000

EXTRA FEATURE/ACCESSORY INCL.

Dimmable with remote control: Yes
LED integrated: No
LED lamp(s) included: Yes
Remote control included: No

LIGHT CHARACTERISTICS

Colour rendering index (CRI): ≥ 90
Colour temperature: 2700-6500 K
Warm-up time to 60% light: 2
Luminous efficacy (rated) (nom.): 69
lm/W

MISCELLANEOUS

Especially designed for: Living Room
Dining Room

POWER CONSUMPTION

Voltage: 220-240 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 1.018 kg
Overall height: 123 mm
Overall length: 440 mm
Overall width: 105 mm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Lumen output bulb included: 345
Total lumen output fixture: 1035
Light colour: 2700-6500
Energy class included light source: G
Wattage bulb included: 4.9
Maximum wattage replacement bulb:
5
IP code: IP20 | Finger-protected
Class of protection: Class I – Earthed
Light source replaceable: Yes
Number of light sources: 3

WHAT'S SUPPORTED

Compatible with Effects feature: Yes
WiFi: Wireless G
Defined support period: Minimum of
60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth
WiFi (2.4GHz)



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

EAN:

wizconnected.com