




IMAGEO 1x adjustable spotlight

Highlight your home's decor using the adjustable spot and colourful smart light of the WiZ Imageo smart build-on spotlight in black. Use with your existing Wi-Fi to control with the WiZ app or your voice.

PRODUCT HIGHLIGHTS

- Full colour
- Plate Dimensions: Ø8 cm
- IP20/Metal/Black



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!




Matter Certified

This product is Matter certified. You can set it up and control it with your preferred smart home platform and make it work seamlessly with other Matter Certified devices.



Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and get the lights to turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.



Create your perfect light scene

Make your own mix of different colour and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.



Millions of colours and changing light modes to make your day

Choose any light colour you like or simply apply a dynamic light mode that we've designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energising cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Lamp shape: Rectangle

DESIGN AND FINISHING

Colour: Black
Material: Metal

DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000

EXTRA FEATURE/ACCESSORY INCL.

Adjustable spot head: Yes
Dimmable with remote control: Yes
LED integrated: No
LED lamp(s) included: Yes
Remote control included: No

LIGHT CHARACTERISTICS

Colour rendering index (CRI): 90
Warm-up time to 60% light: <2

MISCELLANEOUS

Especially designed for: Functional

OTHER CHARACTERISTICS

Efficacy: 69 lm/W

POWER CONSUMPTION

Voltage: 220-240 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.278 kg
Height: 12.3 cm
Length: 8 cm
Width: 10.5 cm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Lifetime up to: 15,000 h
Lumen output bulb included: 345 lm
Total lumen output fixture: 345
Light colour: 2200-6500 (RGB)
Fixture dimmable: Wireless Dim – Do not use with a dimmer
LED: Yes
Built-in LED: Yes
Energy class included light source: G
Number of bulbs: 1
Wattage bulb included: 4.9
Maximum wattage replacement bulb: 5 W
IP code: IP20
Class of protection: Class I
Light source replaceable: Yes



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

EAN:

wizconnected.com