

Bar Linear Light

If you have a shelf or corner that needs accent lighting, try our Bar light. This slim bar radiates plenty of colours and is easy to fit in small spaces. Simply tilt it on one of its sides to adjust the light angle. Do you prefer a longer light? Connect a second bar to double the effect.



PRODUCT HIGHLIGHTS

- Full colour
- Versatile bar light
- Easy plug and play



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!




Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and get the lights to turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.



Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



Create your perfect light scene

Make your own mix of different colour and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.



Millions of colours and changing light modes to make your day

Choose any light colour you like or simply apply a dynamic light mode that we've designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energising cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Lamp shape: Rectangle

DESIGN AND FINISHING

Colour: White
Material: Plastic

DURABILITY

Average life (at 2.7 hrs/day): 25 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000

EXTRA FEATURE/ACCESSORY INCL.

Adjustable spot head: No
Dimmable with remote control: Yes
LED integrated: Yes
On/off switch on wire: No
Remote control included: No

LIGHT CHARACTERISTICS

Colour consistency: 6 SDCM
Colour rendering index (CRI): 80
Warm-up time to 60% light: <2

MISCELLANEOUS

Especially designed for: Functional

OTHER CHARACTERISTICS

Lamp current: 40 mA
Efficacy: 72 lm/W

POWER CONSUMPTION

Power factor: 0.7
Voltage: 220-240 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.35 kg
Height: 4.2 cm
Length: 30 cm
Width: 4.5 cm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Lifetime up to: 25,000 h
Total lumen output fixture: 400
Light colour: 2200-6500 (RGB)
Fixture dimmable: Wireless Dim – Do not use with a dimmer
LED: Yes
Built-in LED: Yes
Wattage bulb included: 5.5
IP code: IP20
Class of protection: Class II



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

EAN:

wizconnected.com