

## Pole Floor Light

Enjoy coloured, wide-angle wall-wash effects with this Pole LED floor light. Standing tall in the corner, it creates ambience thanks to dual zone lighting producing a soft, gradient light. With its foot removed, placed horizontally under your couch or behind your TV, it invites you to unwind with your family.

## PRODUCT HIGHLIGHTS

- Full colour
- Versatile bar light
- Dual zone light effect





### Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



### Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and get the lights to turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.



### Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.




### Millions of colours and changing light modes to make your day

Choose any light colour you like or simply apply a dynamic light mode that we've designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



### Set the right ambience with tunable warm to cool white light

Choose from a wide range of energising cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



### Control smart lighting the way you like it

WiZ enables you to control smart lighting in multiple ways. Adjust lights with your smartphone, voice, the WiZ remote control or by using the existing wall switch to toggle between two favourite modes. Works with Google Home, Alexa and Siri Shortcuts.



# SPECIFICATIONS

## BULB CHARACTERISTICS

Intended use: Indoor  
Dimmable: Yes

## DESIGN AND FINISHING

Colour: White  
Material: Plastic

## DURABILITY

Average life (at 2.7 hrs/day): 25 year(s)  
Lumen maintenance factor: 70%  
Number of switch cycles: 50,000  
Nominal lifetime: 25,000

## EXTRA FEATURE/ACCESSORY INCL.

Dimmable with remote control: Yes  
LED integrated: Yes  
On/off switch on wire: No  
Remote control included: No

## LIGHT CHARACTERISTICS

Colour consistency: 6 SDCM  
Colour rendering index (CRI):  $\geq 80$   
Colour temperature: 2200-6500 K  
Warm-up time to 60% light: 2  
Luminous efficacy (rated) (nom.): 83  
lm/W

## MISCELLANEOUS

Especially designed for: Living Room  
Dining Room Bedroom Children's  
room

## OTHER CHARACTERISTICS

Lamp current: 90 mA

## POWER CONSUMPTION

Power factor: 0.7  
Voltage: 220-240 V

## PRODUCT DIMENSIONS AND WEIGHT

Net weight: 1.5 kg  
Overall height: 1,500 mm

## SERVICE

Warranty: 2 year(s)

## TECHNICAL SPECIFICATIONS

Diameter: 180 mm  
Total lumen output fixture: 1080  
Light colour: 2200-6500 (RGB)  
Wattage bulb included: 13  
IP code: IP20 | Finger-protected  
Class of protection: Class II – Double  
Insulated

## WHAT'S SUPPORTED

Compatible with Effects feature: Yes  
WiFi: Wireless G  
Defined support period: Minimum of  
60 months after introduction date  
Max. number of accessories: 9999  
Communication protocol: Bluetooth  
WiFi (2.4GHz)



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

EAN:

[wizconnected.com](https://wizconnected.com)